

# RCT6-LTC-5A-RNA

---



RCT6, RADIAX® Coaxial Radiating Cable with Bump, 70–960 MHz, tuned foil, 1-1/4 in, black non-halogenated, fire retardant polyolefin jacket

## Product Classification

<b>Product Type</b>	Radiating cable
<b>Product Brand</b>	RADIAX®
<b>Product Series</b>	RCT6

## General Specifications

<b>Polarization</b>	Vertical
<b>Cable Type</b>	Radiating Mode (RCT) Series
<b>Jacket Color</b>	Black

## Dimensions

<b>Diameter Over Jacket, maximum</b>	39.116 mm   1.54 in
<b>Inner Conductor OD</b>	14.208 mm   0.559 in
<b>Outer Conductor OD</b>	34.036 mm   1.34 in
<b>Nominal Size</b>	1-1/4 in
<b>Recommended Distance from the Wall</b>	101.6 mm   4 in
<b>Recommended Hanger Spacing</b>	1.3 m   4.265 ft

## Electrical Specifications

<b>Attenuation Test Method</b>	IEC 61196-4
<b>Attenuation Tolerance</b>	±5%
<b>Cable Impedance</b>	50 ohm ±2 ohm
<b>dc Resistance, Inner Conductor</b>	1.74 ohms/km   0.53 ohms/kft
<b>dc Resistance, Outer Conductor</b>	2.953 ohms/km   0.9 ohms/kft
<b>dc Test Voltage</b>	8500 V

# RCT6-LTC-5A-RNA

<b>Insulation Resistance</b>	100000 MOhms-km
<b>Jacket Spark Test Voltage (rms)</b>	10000 V
<b>Operating Frequency Band</b>	50 – 1000 MHz
<b>Optimum Operating Frequency Band</b>	70 – 960 MHz
<b>Peak Power</b>	180 kW
<b>Stop Bands</b>	520 – 600 MHz
<b>Velocity</b>	91 %
<b>VSWR Installed, typical, 50–960 MHz</b>	1.3
<b>VSWR on Reel, typical</b>	1.43

## Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Coupling Loss 50%	Coupling Loss 95%
75.0	0.8	0.24	59	71
100.0	0.9	0.27	61	70
150.0	1.1	0.33	67	80
350.0	1.7	0.52	70	76
450.0	1.9	0.58	66	70
800.0	2.7	0.83	62	66
900.0	3	0.91	63	67

## Material Specifications

<b>Dielectric Material</b>	Foam PE
<b>Jacket Material</b>	Non-halogenated, fire retardant polyolefin
<b>Inner Conductor Material</b>	Corrugated copper tube
<b>Outer Conductor Material</b>	Copper foil

## Mechanical Specifications

<b>Minimum Bend Radius, single Bend</b>	381 mm   15 in
<b>Tensile Strength</b>	168 kg   370.376 lb
<b>Bending Moment</b>	15.5 N-m   137.187 in lb
<b>Coupling Loss Test Method</b>	IEC 61196-4
<b>Coupling Loss Tolerance</b>	±5 dB
<b>Flat Plate Crush Strength</b>	1.4 kg/mm   78.396 lb/in
<b>Indication of Slot Alignment</b>	Yes—bumps face the wall

# RCT6-LTC-5A-RNA

---

## Environmental Specifications

<b>Installation temperature</b>	-30 °C to +60 °C (-22 °F to +140 °F)
<b>Operating Temperature</b>	-30 °C to +80 °C (-22 °F to +176 °F)
<b>Storage Temperature</b>	-30 °C to +80 °C (-22 °F to +176 °F)
<b>Attenuation, Ambient Temperature</b>	68 °F   20 °C
<b>Average Power, Ambient Temperature</b>	104 °F   40 °C
<b>Average Power, Inner Conductor Temperature</b>	212 °F   100 °C
<b>Fire Retardancy Test Method</b>	IEC 60332-1-2   IEC 60332-3C-24
<b>Smoke Index Test Method</b>	IEC 61034
<b>Toxicity Index Test Method</b>	IEC 60754-1   IEC 60754-2

## Packaging and Weights

<b>Cable weight</b>	0.64 kg/m   0.43 lb/ft
---------------------	------------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

