



75 Ohm QR® Trunk and Distribution Cable, black PE jacket with co-extruded green stripe

- \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

## Product Classification

Regional Availability	North America
Product Type	Coaxial hardline cable
Product Brand	QR®
Government Requirements	Build America Buy America (BABA) compliant*

## General Specifications

Cable Type	715 Series
Construction Type	Welded
Jacket Color	Black with co-extruded green stripe
Location of Manufacturing	Catawba, North Carolina
Short Description	QR 715 JCAT G SM MT PR7280

## Dimensions

Cable Length	914.4 m   3000 ft
Diameter Over Center Conductor, nominal	4.216 mm   0.166 in
Diameter Over Dielectric, nominal	17.424 mm   0.686 in
Diameter Over Jacket, nominal	19.939 mm   0.785 in
Diameter Over Outer Conductor, nominal	18.161 mm   0.715 in
Jacket Thickness, nominal	0.889 mm   0.035 in
Outer Conductor Thickness, nominal	0.368 mm   0.014 in

## Electrical Specifications

Capacitance	50.197 pF/m   15.3 pF/ft
Capacitance Tolerance	±1.0 pF/ft

# 5560502 | QR® 715 JCAT G SM MT

Characteristic Impedance	75 ohm
Characteristic Impedance Tolerance	±2 ohm
dc Resistance Note	Nominal values based on a standard condition of 20 °C (68 °F)
dc Resistance, Inner Conductor, nominal	1.903 ohms/km   0.58 ohms/kft
dc Resistance, Loop, nominal	3.281 ohms/km   1 ohms/kft
dc Resistance, Outer Conductor, nominal	1.378 ohms/km   0.42 ohms/kft
Jacket Spark Test Voltage	5000 Vac
Nominal Velocity of Propagation (NVP)	88 %
Operating Frequency Band	5–3000 MHz
Structural Return Loss	24 dB @ 1003–1218 MHz   24 dB @ 1219–1794 MHz   30 dB @ 5–1002 MHz
Structural Return Loss, Grade N	≥24 dB @ 1003–1218 MHz   ≥24 dB @ 1219–1794 MHz   ≥30 dB @ 5–1002 MHz

## Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5.0	0.36	0.11
55.0	1.21	0.37
85.0	1.51	0.46
204.0	2.4	0.73
211.0	2.43	0.74
250.0	2.66	0.81
300.0	2.92	0.89
350.0	3.18	0.97
400.0	3.44	1.05
450.0	3.67	1.12
500.0	3.9	1.19
550.0	4.1	1.25
600.0	4.3	1.31
750.0	4.89	1.49
865.0	5.31	1.62
1002.0	5.76	1.75
1218.0	6.43	1.96
1500.0	7.44	2.27
1794.0	8.3	2.53

# 5560502 | QR® 715 JCAT G SM MT

1800.0	8.32	2.54
2000.0	8.88	2.71
2200.0	9.42	2.87
2500.0	10.21	3.11
2700.0	10.72	3.27
3000.0	11.46	3.49

## Material Specifications

Center Conductor Material	Copper-clad aluminum
Dielectric Material	Foam PE
Jacket Material	PE
Outer Conductor Material	Aluminum

## Mechanical Specifications

Minimum Bend Radius, bonded	127 mm   5 in
Pulling Tension, maximum	154.221 kg   340 lb

## Environmental Specifications

Environmental Space	Aerial
---------------------	--------

## Packaging and Weights

Packaging Type	Reel
Weight, gross	305.074 kg/km   205 lb/kft

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system