

# AVA5-50

---



AVA5-50, HELIAX® Andrew Virtual Air™ Coaxial Cable, corrugated copper, 7/8 in, black PE jacket (Halogen free jacketing non-fire-retardant)

## Product Classification

<b>Product Type</b>	Coaxial wireless cable
<b>Product Brand</b>	HELIAX®
<b>Product Series</b>	AVA5-50
<b>Ordering Note</b>	North America alternative part number is AVA5P-50-C (520093702 /00)   Not available in the United States or Canada

## General Specifications

<b>Product Number</b>	520096102/00   SZ520096102/00
<b>Flexibility</b>	Standard
<b>Jacket Color</b>	Black
<b>Performance Note</b>	Attenuation values typical, guaranteed within 5%
<b>Specification Sheet Revision Level</b>	B

## Dimensions

<b>Diameter Over Dielectric</b>	24.13 mm   0.95 in
<b>Diameter Over Jacket</b>	27.991 mm   1.102 in
<b>Inner Conductor OD</b>	9.449 mm   0.372 in
<b>Outer Conductor OD</b>	25.4 mm   1 in
<b>Nominal Size</b>	7/8 in

## Electrical Specifications

<b>Cable Impedance</b>	50 ohm $\pm$ 1 ohm
<b>Capacitance</b>	73 pF/m   22.25 pF/ft
<b>dc Resistance, Inner Conductor</b>	1.435 ohms/km   0.437 ohms/kft
<b>dc Resistance, Outer Conductor</b>	1.116 ohms/km   0.34 ohms/kft

# AVA5-50

---

<b>dc Test Voltage</b>	6000 V
<b>Inductance</b>	0.184 $\mu$ H/m   0.056 $\mu$ H/ft
<b>Insulation Resistance</b>	100000 MOhms-km
<b>Jacket Spark Test Voltage (rms)</b>	8000 V
<b>Operating Frequency Band</b>	1 – 5000 MHz
<b>Peak Power</b>	91 kW
<b>Velocity</b>	91 %

## Attenuation

<b>Frequency (MHz)</b>	<b>Attenuation (dB/100 m)</b>	<b>Attenuation (dB/100 ft)</b>	<b>Average Power (kW)</b>
1.0	0.113	0.034	74.43
1.5	0.138	0.042	60.73
2.0	0.16	0.049	52.56
10.0	0.359	0.11	23.37
20.0	0.51	0.156	16.46
30.0	0.627	0.191	13.39
50.0	0.814	0.248	10.32
85.0	1.068	0.326	7.86
88.0	1.088	0.332	7.72
100.0	1.162	0.354	7.23
108.0	1.209	0.368	6.95
150.0	1.433	0.437	5.86
174.0	1.548	0.472	5.43
200.0	1.665	0.507	5.05
204.0	1.682	0.513	4.99
300.0	2.059	0.628	4.08
400.0	2.398	0.731	3.5
450.0	2.553	0.778	3.29
460.0	2.583	0.787	3.25
500.0	2.7	0.823	3.11
512.0	2.735	0.834	3.07
600.0	2.977	0.907	2.82
700.0	3.235	0.986	2.6
800.0	3.478	1.06	2.42

# AVA5-50

---

824.0	3.534	1.077	2.38
894.0	3.694	1.126	2.27
960.0	3.841	1.171	2.19
1000.0	3.927	1.197	2.14
1218.0	4.377	1.334	1.92
1250.0	4.44	1.353	1.89
1500.0	4.912	1.497	1.71
1700.0	5.268	1.605	1.59
1794.0	5.429	1.655	1.55
1800.0	5.439	1.658	1.54
2000.0	5.771	1.759	1.46
2100.0	5.933	1.808	1.42
2200.0	6.091	1.856	1.38
2300.0	6.247	1.904	1.34
2500.0	6.55	1.996	1.28
2700.0	6.845	2.086	1.23
3000.0	7.272	2.217	1.15
3400.0	7.819	2.383	1.07
3600.0	8.083	2.464	1.04
3700.0	8.213	2.503	1.02
3800.0	8.342	2.542	1.01
3900.0	8.47	2.581	0.99
4000.0	8.596	2.62	0.98
4100.0	8.722	2.658	0.96
4200.0	8.846	2.696	0.95
4300.0	8.969	2.734	0.94
4400.0	9.092	2.771	0.92
4500.0	9.213	2.808	0.91
4600.0	9.333	2.845	0.9
4700.0	9.453	2.881	0.89
4800.0	9.572	2.917	0.88
4900.0	9.689	2.953	0.87
5000.0	9.806	2.989	0.86

## Material Specifications

**Dielectric Material**

Foam PE

# AVA5-50

---

<b>Jacket Material</b>	PE
<b>Inner Conductor Material</b>	Copper tube
<b>Outer Conductor Material</b>	Corrugated copper

## Mechanical Specifications

<b>Minimum Bend Radius, multiple Bends</b>	254 mm   10 in
<b>Minimum Bend Radius, single Bend</b>	127 mm   5 in
<b>Number of Bends, minimum</b>	15
<b>Number of Bends, typical</b>	30
<b>Tensile Strength</b>	159 kg   350.535 lb
<b>Bending Moment</b>	19 N-m   168.164 in lb
<b>Flat Plate Crush Strength</b>	1.3 kg/mm   72.797 lb/in

## Environmental Specifications

<b>Installation temperature</b>	-40 °C to +60 °C (-40 °F to +140 °F)
<b>Operating Temperature</b>	-55 °C to +85 °C (-67 °F to +185 °F)
<b>Storage Temperature</b>	-70 °C to +85 °C (-94 °F to +185 °F)
<b>Attenuation, Ambient Temperature</b>	68 °F   20 °C
<b>Average Power, Ambient Temperature</b>	104 °F   40 °C
<b>Average Power, Inner Conductor Temperature</b>	212 °F   100 °C

## Packaging and Weights

<b>Cable weight</b>	0.45 kg/m   0.302 lb/ft
---------------------	-------------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

