

FSJ1-50A, HELIAX® Superflexible Low Density Foam Premium Coaxial Cable, corrugated copper, 1/4 in, black PE jacket

Product Classification

 Product Type
 Coaxial wireless cable

 Product Brand
 HELIAX® | SureFlex®

Product Series FSJ1-50A

General Specifications

Flexibility Superflexible

Jacket Color Black

Performance Note Attenuation values typical, guaranteed within 5%

Dimensions

Cable Length 0 m | 0 ft

 Diameter Over Dielectric
 4.826 mm | 0.19 in

 Diameter Over Jacket
 7.366 mm | 0.29 in

 Inner Conductor OD
 1.905 mm | 0.075 in

 Outer Conductor OD
 6.35 mm | 0.25 in

Nominal Size 1/4 in

Electrical Specifications

Cable Impedance 50 ohm ±1 ohm

 $\textbf{Capacitance} \hspace{1.5cm} 79.4 \hspace{.1cm} \text{pF/m} \hspace{.1cm} | \hspace{.1cm} 24.201 \hspace{.1cm} \text{pF/ft}$

dc Resistance, Inner Conductor9.843 ohms/km | 3 ohms/kft

dc Resistance, Outer Conductor 7.216 ohms/km | 2.199 ohms/kft

dc Test Voltage 1600 V

 $\label{eq:local_phi} \mbox{Inductance} \qquad \qquad 0.2 \ \mu\mbox{H/m} \ \mid \ 0.061 \ \mu\mbox{H/ft}$

Insulation Resistance 100000 MOhms-km

Jacket Spark Test Voltage (rms) 5000 V

Operating Frequency Band 1 – 18000 MHz

ANDREW® an Amphenol company

Peak Power6.4 kWVelocity82 %

VSWR/Return Loss

 Frequency Band
 VSWR
 Return Loss (dB)

 806-960 MHz
 1.101
 26.36

 1700-2200 MHz
 1.101
 26.36

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)
1.0	0.577	0.176	6.4
1.5	0.707	0.215	6.4
2.0	0.816	0.249	6.4
10.0	1.833	0.559	3.99
20.0	2.6	0.792	2.81
30.0	3.192	0.973	2.29
50.0	4.136	1.261	1.77
85.0	5.419	1.652	1.35
88.0	5.516	1.681	1.33
100.0	5.889	1.795	1.24
108.0	6.125	1.867	1.19
150.0	7.25	2.21	1.01
174.0	7.825	2.385	0.93
200.0	8.408	2.563	0.87
204.0	8.495	2.589	0.86
300.0	10.373	3.162	0.71
400.0	12.051	3.673	0.61
450.0	12.817	3.906	0.57
460.0	12.965	3.952	0.56
500.0	13.545	4.128	0.54
512.0	13.715	4.18	0.53
600.0	14.909	4.544	0.49
700.0	16.175	4.93	0.45
800.0	17.362	5.292	0.42
824.0	17.637	5.376	0.41

ANDREW®
an Amphenol company

894.0	18.42	5.614	0.4
960.0	19.134	5.832	0.38
1000.0	19.556	5.96	0.37
1218.0	21.738	6.626	0.34
1250.0	22.044	6.719	0.33
1500.0	24.326	7.414	0.3
1700.0	26.038	7.936	0.28
1794.0	26.813	8.172	0.27
1800.0	26.862	8.187	0.27
2000.0	28.455	8.673	0.26
2100.0	29.227	8.908	0.25
2200.0	29.984	9.139	0.24
2300.0	30.727	9.365	0.24
2500.0	32.174	9.806	0.23
2700.0	33.576	10.233	0.22
3000.0	35.602	10.851	0.21
3400.0	38.183	11.638	0.19
3600.0	39.428	12.017	0.19
3700.0	40.041	12.204	0.18
3800.0	40.647	12.389	0.18
3900.0	41.247	12.571	0.18
4000.0	41.841	12.753	0.17
4100.0	42.429	12.932	0.17
4200.0	43.012	13.11	0.17
4300.0	43.59	13.286	0.17
4400.0	44.163	13.46	0.17
4500.0	44.73	13.633	0.16
4600.0	45.293	13.805	0.16
4700.0	45.852	13.975	0.16
4800.0	46.405	14.144	0.16
4900.0	46.955	14.311	0.16
5000.0	47.5	14.477	0.15
6000.0	52.747	16.077	0.14
8000.0	62.37	19.01	0.12
8800.0	65.974	20.108	0.11

10000.0	71.173	21.693	0.1
12000.0	79.393	24.198	0.09
14000.0	87.172	26.569	0.08
15800.0	93.872	28.611	0.08
16000.0	94.601	28.833	0.08
18000.0	101.745	31.01	0.07

Material Specifications

 Dielectric Material
 Foam PE

 Jacket Material
 PE

Inner Conductor Material Copper-clad aluminum wire

Outer Conductor Material Corrugated copper

Mechanical Specifications

Minimum Bend Radius, multiple Bends25.4 mm | 1 inMinimum Bend Radius, single Bend25.4 mm | 1 in

Number of Bends, minimum 15 Number of Bends, typical 20

 Tensile Strength
 68 kg | 149.914 lb

 Bending Moment
 0.7 N-m | 6.196 in lb

Flat Plate Crush Strength 1.8 kg/mm | 100.795 lb/in

Environmental Specifications

Installation temperature-40 °C to +60 °C (-40 °F to +140 °F)Operating Temperature-55 °C to +85 °C (-67 °F to +185 °F)Storage Temperature-70 °C to +85 °C (-94 °F to +185 °F)

Attenuation, Ambient Temperature68 °F | 20 °CAverage Power, Ambient Temperature104 °F | 40 °CAverage Power, Inner Conductor Temperature212 °F | 100 °C

Packaging and Weights

Cable weight 0.07 kg/m | 0.047 lb/ft

Regulatory Compliance/Certifications



Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

