


# FSJ2P-50-43B

---



FSJ2-50, HELIAX® Superflexible Foam Premium Coaxial Cable, corrugated copper, 3/8 in, black PE jacket

## Product Classification

<b>Product Type</b>	Coaxial wireless cable
<b>Product Brand</b>	HELIAX®   SureFlex®
<b>Product Series</b>	FSJ2-50

## General Specifications

<b>Flexibility</b>	Superflexible
<b>Jacket Color</b>	Black
<b>Performance Note</b>	Attenuation values typical, guaranteed within 5%

## Dimensions

<b>Diameter Over Dielectric</b>	7.112 mm   0.28 in
<b>Diameter Over Jacket</b>	10.668 mm   0.42 in
<b>Inner Conductor OD</b>	2.794 mm   0.11 in
<b>Outer Conductor OD</b>	9.652 mm   0.38 in
<b>Nominal Size</b>	3/8 in

## Electrical Specifications

<b>Cable Impedance</b>	50 ohm ±1 ohm
<b>Capacitance</b>	79.7 pF/m   24.293 pF/ft
<b>dc Resistance, Inner Conductor</b>	4.232 ohms/km   1.29 ohms/kft
<b>dc Resistance, Outer Conductor</b>	4.987 ohms/km   1.52 ohms/kft
<b>dc Test Voltage</b>	2300 V
<b>Inductance</b>	0.2 µH/m   0.061 µH/ft
<b>Insulation Resistance</b>	100000 MOhms-km
<b>Jacket Spark Test Voltage (rms)</b>	4000 V
<b>Operating Frequency Band</b>	1 – 13400 MHz
<b>Peak Power</b>	13.2 kW

# FSJ2P-50-43B

Velocity

83 %

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
680–806 MHz	1.15	23.13
806–960 MHz	1.13	24.29
1427–1535 MHz	1.13	24.29
1700–2300 MHz	1.15	23.13
2535–2655 MHz	1.253	18.99
3400–3800 MHz	1.253	18.99
3800–4100 MHz	1.253	18.99
4400–4900 MHz	1.253	18.99

## Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)
1.0	0.383	0.117	13.2
1.5	0.469	0.143	13.2
2.0	0.542	0.165	13.2
10.0	1.219	0.372	6.97
20.0	1.732	0.528	4.91
30.0	2.128	0.649	3.99
50.0	2.762	0.842	3.08
85.0	3.626	1.105	2.34
88.0	3.691	1.125	2.3
100.0	3.943	1.202	2.16
108.0	4.103	1.25	2.07
150.0	4.864	1.482	1.75
174.0	5.254	1.601	1.62
200.0	5.65	1.722	1.5
204.0	5.709	1.74	1.49
300.0	6.99	2.13	1.22
400.0	8.139	2.481	1.04
450.0	8.665	2.641	0.98
460.0	8.767	2.672	0.97
500.0	9.166	2.794	0.93

# FSJ2P-50-43B

---

<b>512.0</b>	9.283	2.829	0.92
<b>600.0</b>	10.107	3.081	0.84
<b>700.0</b>	10.983	3.347	0.77
<b>800.0</b>	11.807	3.599	0.72
<b>824.0</b>	11.998	3.657	0.71
<b>894.0</b>	12.542	3.823	0.68
<b>960.0</b>	13.04	3.974	0.65
<b>1000.0</b>	13.334	4.064	0.64
<b>1218.0</b>	14.861	4.529	0.57
<b>1250.0</b>	15.075	4.595	0.56
<b>1500.0</b>	16.68	5.084	0.51
<b>1700.0</b>	17.887	5.452	0.48
<b>1794.0</b>	18.436	5.619	0.46
<b>1800.0</b>	18.47	5.629	0.46
<b>2000.0</b>	19.599	5.974	0.43
<b>2100.0</b>	20.147	6.141	0.42
<b>2200.0</b>	20.685	6.305	0.41
<b>2300.0</b>	21.214	6.466	0.4
<b>2500.0</b>	22.247	6.781	0.38
<b>2700.0</b>	23.249	7.086	0.37
<b>3000.0</b>	24.701	7.529	0.34
<b>3400.0</b>	26.558	8.094	0.32
<b>3600.0</b>	27.456	8.368	0.31
<b>3700.0</b>	27.899	8.503	0.3
<b>3800.0</b>	28.337	8.637	0.3
<b>3900.0</b>	28.771	8.769	0.3
<b>4000.0</b>	29.201	8.9	0.29
<b>4100.0</b>	29.628	9.03	0.29
<b>4200.0</b>	30.051	9.159	0.28
<b>4300.0</b>	30.47	9.287	0.28
<b>4400.0</b>	30.886	9.414	0.28
<b>4500.0</b>	31.298	9.539	0.27
<b>4600.0</b>	31.708	9.664	0.27
<b>4700.0</b>	32.114	9.788	0.26
<b>4800.0</b>	32.518	9.911	0.26

# FSJ2P-50-43B

---

<b>4900.0</b>	32.919	10.033	0.26
<b>5000.0</b>	33.316	10.154	0.26
<b>6000.0</b>	37.158	11.325	0.23
<b>8000.0</b>	44.264	13.491	0.19
<b>8800.0</b>	46.943	14.308	0.18
<b>10000.0</b>	50.826	15.491	0.17
<b>12000.0</b>	57.001	17.373	0.15

## Material Specifications

<b>Dielectric Material</b>	Foam PE
<b>Jacket Material</b>	PE
<b>Inner Conductor Material</b>	Copper-clad aluminum wire
<b>Outer Conductor Material</b>	Corrugated copper

## Mechanical Specifications

<b>Minimum Bend Radius, multiple Bends</b>	25.4 mm   1 in
<b>Minimum Bend Radius, single Bend</b>	25.4 mm   1 in
<b>Number of Bends, minimum</b>	30
<b>Number of Bends, typical</b>	50
<b>Tensile Strength</b>	95 kg   209.439 lb
<b>Bending Moment</b>	2.3 N-m   20.357 in lb
<b>Flat Plate Crush Strength</b>	1.8 kg/mm   100.795 lb/in

## Environmental Specifications

<b>Installation temperature</b>	-40 °C to +60 °C (-40 °F to +140 °F)
<b>Operating Temperature</b>	-55 °C to +85 °C (-67 °F to +185 °F)
<b>Storage Temperature</b>	-70 °C to +85 °C (-94 °F to +185 °F)
<b>Attenuation, Ambient Temperature</b>	68 °F   20 °C
<b>Average Power, Ambient Temperature</b>	104 °F   40 °C
<b>Average Power, Inner Conductor Temperature</b>	212 °F   100 °C

## Packaging and Weights

<b>Cable weight</b>	0.12 kg/m   0.081 lb/ft
---------------------	-------------------------

# FSJ2P-50-43B

---

## Regulatory Compliance/Certifications

**Agency****Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

