

Fiber OSP cable, LightScope® ZWP Blown Micro Single Jacket, 144 fiber, All-Dielectric Stranded Loose Tube Arid-Core™ Construction, Gel-filled, Singlemode G.652.D and G.657.A1, Feet jacket marking, Black jacket color

OBSOLETE

This product was discontinued on: December 7, 2020

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber OSP cable
Product Series	B-LN


General Specifications

Cable Type	Stranded loose tube
Construction Type	Non-armored
Subunit Type	Gel-filled
Filler, quantity	0
Jacket Color	Black
Jacket Marking	Feet
Subunit, quantity	12
Fibers per Subunit, quantity	12
Total Fiber Count	144

Dimensions

Buffer Tube/Subunit Diameter	1.45 mm 0.057 in
Diameter Over Jacket	8.4 mm 0.331 in

Representative Image



Material Specifications

Jacket Material

High density polyethylene (HDPE)

Mechanical Specifications

Minimum Bend Radius, loaded	126 mm 4.961 in
Minimum Bend Radius, unloaded	84 mm 3.307 in
Tensile Load, long term, maximum	469 N 105.435 lbf
Tensile Load, short term, maximum	1566 N 352.051 lbf
Compression	10 N/mm 57.101 lb/in
Compression Test Method	IEC 60794-1-21 E3
Flex	25 cycles
Flex Test Method	IEC 60794-1 E6
Impact	0.3 N-m 2.655 in lb
Impact Test Method	IEC 60794-1-21 E4
Strain	See long and short term tensile loads
Strain Test Method	IEC 60794-1-21 E1
Twist	10 cycles
Twist Test Method	IEC 60794-1-21 E7
Vertical Rise, maximum	769 m 2,522.966 ft

Optical Specifications

760245647 | B-144-LN-8W-F12NS/15G

Fiber Type G.652.D | G.652.D and G.657.A1

Environmental Specifications

Installation temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Storage Temperature	-30 °C to +75 °C (-22 °F to +167 °F)
Cable Qualification Standards	IEC 60794-5-10
Environmental Space	Air-blown, microduct
Jacket UV Resistance	UV stabilized
Water Penetration	24 h
Water Penetration Test Method	IEC 60794-1 F4

Environmental Test Specifications

Cable Freeze	-2 °C 28.4 °F
Cable Freeze Test Method	IEC 60794-1 F15
Drip	70 °C 158 °F
Drip Test Method	IEC 60794-1-21 E14
Heat Age	-30 °C to +85 °C (-22 °F to +185 °F)
Heat Age Test Method	IEC 60794-1-22 F9
Low High Bend	-30 °C to +60 °C (-22 °F to +140 °F)
Low High Bend Test Method	IEC 60794-1-21 E11
Temperature Cycle	-30 °C to +70 °C (-22 °F to +158 °F)
Temperature Cycle Test Method	IEC 60794-1-22 F1

Packaging and Weights

Cable weight	63 kg/km 42.334 lb/kft
---------------------	--------------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

CS-8W-250-EMEA – LightScope® ZWP Singlemode Fiber
8W-250um

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable