

CNT-195-FR-600M



CNT-195-FR, CNT® 50 Ohm Braided Coaxial Cable, 600 m, black non-halogenated, fire retardant polyolefin jacket, Dca s2 d2 Compliant

OBSOLETE

Product Classification

Product Type	Braided coaxial cable
Product Brand	CNT®
Product Series	CNT-195

General Specifications

Braid Coverage	89 %
Cable Type	CNT-195
Jacket Color	Black

Dimensions

Cable Length	600 m 1,968.504 ft
Reel Flange	330 mm 12.992 in
Reel Hub	127 mm 5 in
Reel Traverse	305 mm 12.008 in
Diameter Over Dielectric	2.79 mm 0.11 in
Diameter Over Jacket	4.95 mm 0.195 in
Inner Conductor OD	0.94 mm 0.037 in
Outer Conductor OD	3.5 mm 0.138 in
Nominal Size	0.195 in

Electrical Specifications

Cable Impedance	50 ohm
-----------------	--------

CNT-195-FR-600M

Capacitance	79.7 pF/m 24.293 pF/ft
dc Resistance, Inner Conductor	24.94 ohms/km 7.602 ohms/kft
dc Resistance, Outer Conductor	16.08 ohms/km 4.901 ohms/kft
dc Test Voltage	1500 V
Jacket Spark Test Voltage (rms)	3000 V
Maximum Frequency	37.9 GHz
Operating Frequency Band	30 – 6000 MHz
Peak Power	2.5 kW
Shielding Effectiveness	90 dB
Velocity	75 %

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
30.0	6.56	2
50.0	8.53	2.6
150.0	14.43	4.4
220.0	17.71	5.4
450.0	25.58	7.8
900.0	36.41	11.1
1800.0	52.48	16
2500.0	62.32	19
3000.0	68.58	20.91
4000.0	79.87	24.35
4500.0	85.05	25.93
5000.0	89.97	27.43
5200.0	91.87	28.01
5500.0	94.66	28.86
5800.0	97.42	29.7
6000.0	99.19	30.24

Material Specifications

Braid Material	Tinned copper
Dielectric Material	Foam PE
Jacket Material	Non-halogenated, fire retardant polyolefin

CNT-195-FR-600M

Inner Conductor Material	Copper
Shield Tape Material	Aluminum

Mechanical Specifications

Minimum Bend Radius, single Bend	12.7 mm 0.5 in
Tensile Strength	18 kg 39.683 lb
Bending Moment	0.3 N-m 2.655 in lb
Flat Plate Crush Strength	0.3 kg/mm 16.799 lb/in

Environmental Specifications

Installation temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Operating Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Storage Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
EN50575 CPR Cable EuroClass Fire Performance	Dca
EN50575 CPR Cable EuroClass Smoke Rating	s2
EN50575 CPR Cable EuroClass Droplets Rating	d2
Smoke Index Test Method	IEC 61034
Toxicity Index Test Method	IEC 60754-2

Packaging and Weights

Packaging Type	Reel
Weight, gross	20.1 kg 44.313 lb

Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

