

# RCT7-WBC-4A-RNA

---



RCT7, RADIAX® Coaxial Radiating Cable with Bump, 50–2700 MHz, tuned foil, 1-5/8 in, black non-halogenated, fire retardant polyolefin jacket

**OBSOLETE**

## Product Classification

<b>Product Type</b>	Radiating cable
<b>Product Brand</b>	RADIAX®
<b>Product Series</b>	RCT7

## General Specifications

<b>Polarization</b>	Vertical
<b>Cable Type</b>	Radiating Mode (RCT) Series
<b>Jacket Color</b>	Black

## Dimensions

<b>Diameter Over Jacket, maximum</b>	49.784 mm   1.96 in
<b>Inner Conductor OD</b>	18.161 mm   0.715 in
<b>Outer Conductor OD</b>	43.815 mm   1.725 in
<b>Nominal Size</b>	1-5/8 in
<b>Recommended Distance from the Wall</b>	101.6 mm   4 in
<b>Recommended Hanger Spacing</b>	1.3 m   4.265 ft

## Electrical Specifications

<b>Attenuation Test Method</b>	IEC 61196-4
<b>Attenuation Tolerance</b>	±5%
<b>Cable Impedance</b>	50 ohm ±2 ohm
<b>dc Resistance, Inner Conductor</b>	1.435 ohms/km   0.437 ohms/kft

# RCT7-WBC-4A-RNA

<b>dc Resistance, Outer Conductor</b>	1.969 ohms/km   0.6 ohms/kft
<b>dc Test Voltage</b>	15000 V
<b>Insulation Resistance</b>	100000 MOhms-km
<b>Jacket Spark Test Voltage (rms)</b>	10000 V
<b>Operating Frequency Band</b>	50 – 2700 MHz
<b>Optimum Operating Frequency Band</b>	1710 – 2700 MHz   698 – 960 MHz
<b>Peak Power</b>	302 kW
<b>Stop Bands</b>	1090 – 1145 MHz   1635 – 1705 MHz   2180 – 2270 MHz   545 – 570 MHz
<b>Velocity</b>	93 %
<b>VSWR Installed, typical, 1700–2700 MHz</b>	1.38
<b>VSWR Installed, typical, 50–960 MHz</b>	1.3
<b>VSWR on Reel, typical</b>	1.43

## Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Coupling Loss 50%	Coupling Loss 95%
75.0	0.53	0.16	69	79
100.0	0.6	0.18	67	77
150.0	0.75	0.23	76	82
350.0	1.2	0.37	78	84
450.0	1.34	0.41	74	78
500.0	1.44	0.44	76	86
600.0	1.6	0.48	72	81
700.0	1.75	0.53	72	77
800.0	1.9	0.58	70	74
900.0	2.05	0.62	71	76
960.0	2.14	0.65	69	73
1700.0	3.2	0.98	64	71
1800.0	3.32	1.01	64	69
1900.0	3.46	1.05	61	68
2000.0	3.6	1.1	59	69
2100.0	3.79	1.16	61	69
2200.0	4.02	1.23	61	68
2300.0	4.29	1.31	61	67

# RCT7-WBC-4A-RNA

2400.0	4.49	1.37	61	67
2500.0	4.81	1.47	61	68
2600.0	5.11	1.56	60	69
2700.0	5.6	1.71	58	67

## Material Specifications

<b>Dielectric Material</b>	Foam PE
<b>Jacket Material</b>	Non-halogenated, fire retardant polyolefin
<b>Inner Conductor Material</b>	Corrugated copper tube
<b>Outer Conductor Material</b>	Copper foil

## Mechanical Specifications

<b>Minimum Bend Radius, single Bend</b>	508 mm   20 in
<b>Tensile Strength</b>	215 kg   473.993 lb
<b>Bending Moment</b>	16 N-m   141.612 in lb
<b>Coupling Loss Test Method</b>	IEC 61196-4
<b>Coupling Loss Tolerance</b>	±5 dB
<b>Flat Plate Crush Strength</b>	0.8 kg/mm   44.798 lb/in
<b>Indication of Slot Alignment</b>	Yes—bumps face the wall

## Environmental Specifications

<b>Installation temperature</b>	-30 °C to +60 °C (-22 °F to +140 °F)
<b>Operating Temperature</b>	-30 °C to +80 °C (-22 °F to +176 °F)
<b>Storage Temperature</b>	-30 °C to +80 °C (-22 °F to +176 °F)
<b>Attenuation, Ambient Temperature</b>	68 °F   20 °C
<b>Average Power, Ambient Temperature</b>	104 °F   40 °C
<b>Average Power, Inner Conductor Temperature</b>	212 °F   100 °C
<b>Fire Retardancy Test Method</b>	IEC 60332-1-2   IEC 60332-3C-24
<b>Smoke Index Test Method</b>	IEC 61034
<b>Toxicity Index Test Method</b>	IEC 60754-1   IEC 60754-2

## Packaging and Weights

<b>Cable weight</b>	0.78 kg/m   0.524 lb/ft
---------------------	-------------------------

# RCT7-WBC-4A-RNA

---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant