



75 Ohm QR® Trunk and Distribution Cable, black flame retardant PE jacket with co-extruded red stripe

- \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Coaxial hardline cable
<b>Product Brand</b>	QR®
<b>Government Funding</b>	Build America Buy America (BABA) compliant*

## General Specifications

<b>Cable Type</b>	540 Series
<b>Construction Type</b>	Welded
<b>Jacket Color</b>	Black with co-extruded red stripe
<b>Location of Manufacturing</b>	Catawba, North Carolina
<b>Short Description</b>	QR 540 JCART R SM PR2351

## Dimensions

<b>Cable Length</b>	1,127.76 m   3700 ft
<b>Diameter Over Center Conductor, nominal</b>	3.15 mm   0.124 in
<b>Diameter Over Dielectric, nominal</b>	13.056 mm   0.514 in
<b>Diameter Over Jacket, nominal</b>	15.494 mm   0.61 in
<b>Diameter Over Outer Conductor, nominal</b>	13.716 mm   0.54 in
<b>Jacket Thickness, nominal</b>	0.889 mm   0.035 in
<b>Outer Conductor Thickness, nominal</b>	0.343 mm   0.014 in

## Electrical Specifications

<b>Capacitance</b>	50.197 pF/m   15.3 pF/ft
<b>Capacitance Tolerance</b>	±1.0 pF/ft

# 5518702 | QR® 540 JCART R

<b>Characteristic Impedance</b>	75 ohm
<b>Characteristic Impedance Tolerance</b>	±2 ohm
<b>dc Resistance Note</b>	Nominal values based on a standard condition of 20 °C (68 °F)
<b>dc Resistance, Inner Conductor, nominal</b>	3.346 ohms/km   1.02 ohms/kft
<b>dc Resistance, Loop, nominal</b>	5.282 ohms/km   1.61 ohms/kft
<b>dc Resistance, Outer Conductor, nominal</b>	1.936 ohms/km   0.59 ohms/kft
<b>Jacket Spark Test Voltage</b>	5000 Vac
<b>Nominal Velocity of Propagation (NVP)</b>	88 %
<b>Operating Frequency Band</b>	5–3000 MHz
<b>Structural Return Loss</b>	24 dB @ 1003–1218 MHz   24 dB @ 1219–1794 MHz   30 dB @ 5–1002 MHz
<b>Structural Return Loss, Grade N</b>	≥24 dB @ 1003–1218 MHz   ≥24 dB @ 1219–1794 MHz   ≥30 dB @ 5–1002 MHz

## Attenuation

<b>Frequency (MHz)</b>	<b>Attenuation (dB/100 m)</b>	<b>Attenuation (dB/100 ft)</b>
5.0	0.46	0.14
55.0	1.54	0.47
85.0	1.94	0.59
204.0	3.05	0.93
211.0	3.12	0.95
250.0	3.38	1.03
300.0	3.71	1.13
350.0	4.04	1.23
400.0	4.33	1.32
450.0	4.59	1.4
500.0	4.89	1.49
550.0	5.12	1.56
600.0	5.38	1.64
750.0	6.07	1.85
865.0	6.56	2
1002.0	7.12	2.17
1218.0	7.89	2.41
1500.0	9.07	2.76
1794.0	10.11	3.08

# 5518702 | QR® 540 JCART R

---

<b>1800.0</b>	10.13	3.09
<b>2000.0</b>	10.81	3.29
<b>2200.0</b>	11.46	3.49
<b>2500.0</b>	12.41	3.78
<b>2700.0</b>	13.03	3.97
<b>3000.0</b>	13.93	4.24

## Material Specifications

<b>Center Conductor Material</b>	Copper-clad aluminum
<b>Dielectric Material</b>	Foam PE
<b>Jacket Material</b>	PE
<b>Outer Conductor Material</b>	Aluminum

## Mechanical Specifications

<b>Minimum Bend Radius, bonded</b>	101.6 mm   4 in
<b>Pulling Tension, maximum</b>	99.79 kg   220 lb

## Environmental Specifications

<b>Environmental Space</b>	Aerial
<b>Flame Test Listing</b>	NEC Article 820

## Packaging and Weights

<b>Packaging Type</b>	Reel
<b>Weight, gross</b>	187.509 kg/km   126 lb/kft

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system