

LDF4-50, HELIAX® Low Density Foam Premium Coaxial Cable, corrugated copper, 1/2 in, black non-halogenated, fire retardant polyolefin jacket B2ca,sla,dl,al

Product Classification

 Product Type
 Coaxial wireless cable

 Product Brand
 HELIAX® | SureFlex®

Product Series LDF4-50A

Ordering Note ANDREW® standard product in Europe, the Middle East, and Africa | Not

available in the United States or Canada

General Specifications

Product Number 520095102/00 | SZ520095102/00

Flexibility Standard

Jacket Color Black

Performance Note Attenuation values typical, guaranteed within 5%

Dimensions

 Diameter Over Dielectric
 12.954 mm | 0.51 in

 Diameter Over Jacket
 16.002 mm | 0.63 in

 Inner Conductor OD
 4.826 mm | 0.19 in

 Outer Conductor OD
 13.97 mm | 0.55 in

Nominal Size 1/2 in

Electrical Specifications

Cable Impedance 50 ohm ±1 ohm

Capacitance 75.8 pF/m | 23.104 pF/ft

dc Resistance, Inner Conductor1.48 ohms/km | 0.451 ohms/kftdc Resistance, Outer Conductor2.69 ohms/km | 0.82 ohms/kft

dc Test Voltage 4000 V

Inductance 0.19 μH/m | 0.058 μH/ft

Insulation Resistance 100000 MOhms-km



Jacket Spark Test Voltage (rms) 5000 V

Operating Frequency Band 1 – 8800 MHz

 Peak Power
 40 kW

 Velocity
 88 %

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
806-960 MHz	1.101	26.36
1700-2200 MHz	1.101	26.36

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)
1.0	0.211	0.064	36.11
1.5	0.259	0.079	29.46
2.0	0.299	0.091	25.5
10.0	0.672	0.205	11.35
20.0	0.954	0.291	7.99
30.0	1.172	0.357	6.51
50.0	1.521	0.463	5.02
85.0	1.995	0.608	3.82
88.0	2.031	0.619	3.76
100.0	2.169	0.661	3.52
108.0	2.256	0.688	3.38
150.0	2.673	0.815	2.85
174.0	2.887	0.88	2.64
200.0	3.103	0.946	2.46
204.0	3.135	0.956	2.43
300.0	3.835	1.169	1.99
400.0	4.462	1.36	1.71
450.0	4.749	1.447	1.61
460.0	4.804	1.464	1.59
500.0	5.021	1.53	1.52
512.0	5.085	1.55	1.5
600.0	5.533	1.686	1.38
700.0	6.009	1.831	1.27

ANDREW®
an Amphenol company

800.0	6.456	1.968	1.18
824.0	6.56	1.999	1.16
894.0	6.855	2.089	1.11
960.0	7.124	2.171	1.07
1000.0	7.284	2.22	1.05
1218.0	8.11	2.472	0.94
1250.0	8.226	2.507	0.93
1500.0	9.093	2.771	0.84
1700.0	9.744	2.97	0.78
1794.0	10.039	3.06	0.76
1800.0	10.058	3.066	0.76
2000.0	10.666	3.251	0.72
2100.0	10.961	3.341	0.7
2200.0	11.251	3.429	0.68
2300.0	11.535	3.516	0.66
2500.0	12.09	3.685	0.63
2700.0	12.627	3.849	0.6
3000.0	13.407	4.086	0.57
3400.0	14.401	4.389	0.53
3600.0	14.882	4.536	0.51
3700.0	15.118	4.608	0.5
3800.0	15.353	4.679	0.5
3900.0	15.585	4.75	0.49
4000.0	15.815	4.82	0.48
4100.0	16.042	4.889	0.48
4200.0	16.268	4.958	0.47
4300.0	16.492	5.027	0.46
4400.0	16.714	5.094	0.46
4500.0	16.934	5.161	0.45
4600.0	17.153	5.228	0.44
4700.0	17.37	5.294	0.44
4800.0	17.585	5.36	0.43
4900.0	17.798	5.425	0.43
5000.0	18.01	5.489	0.42
6000.0	20.055	6.113	0.38

8000.0 23.826 7.262 0.32 **8800.0** 25.244 7.694 0.3

Material Specifications

Dielectric Material Foam PE

Jacket Material Non-halogenated, fire retardant polyolefin

Inner Conductor Material Copper-clad aluminum wire

Outer Conductor Material Corrugated copper

Mechanical Specifications

Minimum Bend Radius, multiple Bends127 mm | 5 inMinimum Bend Radius, single Bend50.8 mm | 2 in

Number of Bends, minimum 15 Number of Bends, typical 50

 Tensile Strength
 113 kg | 249.122 lb

 Bending Moment
 3.8 N-m | 33.633 in lb

 Flat Plate Crush Strength
 2 kg/mm | 111.995 lb/in

Environmental Specifications

Installation temperature $-40 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Attenuation, Ambient Temperature68 °F | 20 °CAverage Power, Ambient Temperature104 °F | 40 °CAverage Power, Inner Conductor Temperature212 °F | 100 °C

Fire Retardancy Test Method IEC 60332-1-2 | UL 1666/CATVR

Smoke Index Test Method IEC 61034

Toxicity Index Test Method IEC 60754-1 | IEC 60754-2

Packaging and Weights

 $\textbf{Cable weight} \hspace{1.5cm} 0.25\,\text{kg/m} \hspace{0.2cm} \mid \hspace{0.2cm} 0.168\,\text{lb/ft}$

Regulatory Compliance/Certifications

Agency Classification



CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

