

Fiber Indoor/Outdoor Drop Cable, LazrSPEED®, Low Smoke Zero Halogen Single Jacket All-Dielectric Arid-Core, 2-fiber, Gel-filled, Multimode OM3, Feet jacket marking, Black jacket color, Dca flame rating

Product Classification


| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
|------------------------------|--|
| Portfolio | CommScope® |
| Product Type | Fiber drop cable |
| Product Series | Z-DN |
| General Specifications | |
| Cable Type | Riser rated low smoke |
| Construction Type | Non-armored |
| Subunit Type | Gel-filled |
| Jacket Color | Black |
| Jacket Marking | Feet |
| Subunit, quantity | 1 |
| Fibers per Subunit, quantity | 2 |
| Total Fiber Count | 2 |
| Dimensions | |
| Buffer Tube/Subunit Diameter | 2 mm 0.079 in |
| Diameter Over Jacket | 6.1 mm 0.24 in |
| | |

Representative Image

Page 1 of 4

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025





Material Specifications

Jacket Material

Mechanical Specifications

Minimum Bend Radius, loaded 91 mm | 3.583 in Minimum Bend Radius, unloaded 61 mm | 2.402 in Tensile Load, long term, maximum 400 N | 89.924 lbf Tensile Load, short term, maximum 1334 N | 299.895 lbf Compression 10 N/mm | 57.101 lb/in **Compression Test Method** FOTP-41 | IEC 60794-1 E3 Flex 35 cycles Flex Test Method FOTP-104 | IEC 60794-1 E6 Impact 2.21 N-m | 19.56 in lb Impact Test Method FOTP-25 | IEC 60794-1 E4 Strain See long and short term tensile loads Strain Test Method FOTP-33 | IEC 60794-1 E1 Twist 10 cycles Twist Test Method FOTP-85 | IEC 60794-1 E7 Vertical Rise, maximum 927 m | 3,041.339 ft

Optical Specifications

Fiber Type

OM3, LazrSPEED® 300 | OM3, LazrSPEED® 300

Low Smoke Zero Halogen (LSZH)

Page 2 of 4

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025

COMMSCOPE°

Environmental Specifications

| Installation temperature | -20 °C to +60 °C (-4 °F to +140 °F) | |
|--|---|--|
| Operating Temperature | -20 °C to +70 °C (-4 °F to +158 °F) | |
| Storage Temperature | -40 °C to +75 °C (-40 °F to +167 °F) | |
| Cable Qualification Standards | ANSI/ICEA S-110-717 EN 187105 Telcordia GR-409 | |
| EN50575 CPR Cable EuroClass Fire Performance | Dca | |
| EN50575 CPR Cable EuroClass Smoke Rating | s2 | |
| EN50575 CPR Cable EuroClass Droplets Rating | d1 | |
| EN50575 CPR Cable EuroClass Acidity Rating | a1 | |
| Environmental Space | Aerial, lashed Buried Low Smoke Zero Halogen (LSZH) Riser | |
| Flame Test Listing | NEC OFNR-ST1 (ETL) and c(ETL) | |
| Flame Test Method | IEC 60332-3 IEC 60754-2 IEC 61034-2 UL 1666 UL 1685 | |
| Jacket UV Resistance | UV stabilized | |
| Water Penetration | 24 h | |
| Water Penetration Test Method | FOTP-82 IEC 60794-1 F5 | |

Environmental Test Specifications

| Cable Freeze | -2 °C 28.4 °F |
|-------------------------------|-------------------------------------|
| Cable Freeze Test Method | FOTP-98 IEC 60794-1 F15 |
| Drip | 70 °C 158 °F |
| Drip Test Method | FOTP-81 IEC 60794-1 E14 |
| Heat Age Test Method | IEC 60794-1 F9 |
| Low High Bend | -20 °C to +60 °C (-4 °F to +140 °F) |
| Low High Bend Test Method | FOTP-37 IEC 60794-1 E11 |
| Temperature Cycle | -20 °C to +70 °C (-4 °F to +158 °F) |
| Temperature Cycle Test Method | FOTP-3 IEC 60794-1 F1 |
| Packaging and Weights | |

Cable weight

44 kg/km | 29.567 lb/kft

Regulatory Compliance/Certifications

Classification

Agency CENELEC

EN 50575 compliant, Declaration of Performance (DoP) available

Page 3 of 4

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025



ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

CENELEC

Included Products

CS-5L-LT – LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 4 of 4

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025

