

760210245 | HEC-24SM-616M-APV

HELIAX® Hybrid Cable

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Hybrid cable, copper and fiber
Product Brand	HELIAX®

General Specifications

Application	Remote radio head
Cable Type	Wireless feeder
Conductors, quantity	6
Construction Type	Shielded
Fiber Short Description	RFF-16 mm ²
Inner Shield (Tape) Material	Corrugated aluminum
Jacket Color	Black
Outer Shield (Tape) Material	PVC
Strength Members	Glass reinforced plastic rod
Subunit, quantity	2
Fibers per Subunit, quantity	12
Total Fiber Count	24
Water Blocking Method	Water blocking tape(s) Water blocking threads


Dimensions

Buffer Tube/Subunit Diameter	6.604 mm 0.26 in
Diameter Over Jacket	36.322 mm 1.43 in
Conductor Gauge	16 mm ²

Electrical Specifications

dc Resistance Note	Maximum value based on a standard condition of 20 °C (68 °F)
dc Resistance, maximum	1.211 ohms/km 0.369 ohms/kft

Representative Image



Material Specifications

Ripcord Material Para-aramid synthetic fiber

Mechanical Specifications

Minimum Bend Radius, multiple bends, loaded	723.9 mm 28.5 in
Minimum Bend Radius, multiple bends, unloaded	434.34 mm 17.1 in
Minimum Bend Radius, single bend, unloaded	254 mm 10 in
Tensile Load, long term, maximum	1,067.573 N 240 lbf
Tensile Load, short term, maximum	3,558.576 N 800 lbf
Compression	2.25 kg/mm 126 lb/in
Compression Test Method	FOTP-41
Flex Test Method	FOTP-104
Impact	4.34 ft lb 5.884 N-m
Impact Test Method	FOTP-25
Twist	10 cycles
Twist Test Method	FOTP-85

Optical Specifications

Fiber Type G.657.A2/B2 | G.657.A2/B2

Environmental Specifications

Installation temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +80 °C (-40 °F to +176 °F)

760210245 | HEC-24SM-616M-APV

Storage Temperature	-40 °C to +80 °C (-40 °F to +176 °F)
Cable Qualification Standards	ANSI/ICEA S-87-640 Telcordia GR-20 Telcordia GR-409
Environmental Space	Wireless installation

Packaging and Weights

Cable weight	1,711.389 kg/km 1150 lb/kft
---------------------	-------------------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Included Products

CS-8G-MP	-	Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G.657.A2, B2)
----------	---	--

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable