


# HFC-16SM-806-618-APE

---



## HELIAX® Hybrid Cable with aluminum armor

### Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Hybrid cable, copper and fiber
<b>Product Brand</b>	HELIAX®

### General Specifications

<b>Application</b>	Remote radio head
<b>Alarm Wire, quantity</b>	6
<b>Armor Type</b>	Corrugated aluminum
<b>Cable Type</b>	Wireless feeder
<b>Conductors, quantity</b>	8
<b>Construction Type</b>	Armored
<b>Fiber Short Description</b>	RFF – 6AWG
<b>Inner Shield (Tape) Material</b>	Corrugated aluminum
<b>Jacket Color</b>	Black
<b>Outer Shield (Tape) Material</b>	PE
<b>Strength Members</b>	Glass reinforced plastic rod
<b>Subunit, quantity</b>	2
<b>Fibers per Subunit, quantity</b>	8
<b>Total Fiber Count</b>	16
<b>Water Blocking Method</b>	Water blocking tape(s)   Water blocking threads

### Dimensions


# HFC-16SM-806-618-APE

<b>Buffer Tube/Subunit Diameter</b>	6.096 mm   0.24 in
<b>Diameter Over Jacket</b>	30.734 mm   1.21 in
<b>Alarm Wire Gauge</b>	18 AWG
<b>Conductor Gauge</b>	6 AWG

## Electrical Specifications

<b>dc Resistance Note</b>	Maximum value based on a standard condition of 20 °C (68 °F)
<b>dc Resistance, maximum</b>	1.352 ohms/km   0.412 ohms/kft

## Representative Image



## Material Specifications

<b>Ripcord Material</b>	Para-aramid synthetic fiber
-------------------------	-----------------------------

## Mechanical Specifications

<b>Minimum Bend Radius, multiple bends, loaded</b>	614.68 mm   24.2 in
<b>Minimum Bend Radius, multiple bends, unloaded</b>	307.34 mm   12.1 in
<b>Minimum Bend Radius, single bend, unloaded</b>	215.9 mm   8.5 in
<b>Tensile Load, long term, maximum</b>	1,067.573 N   240 lbf
<b>Tensile Load, short term, maximum</b>	3,558.576 N   800 lbf
<b>Compression</b>	2.25 kg/mm   126 lb/in
<b>Compression Test Method</b>	FOTP-41
<b>Flex Test Method</b>	FOTP-104
<b>Impact</b>	2.17 ft lb   2.942 N-m
<b>Impact Test Method</b>	FOTP-25
<b>Twist</b>	10 cycles

# HFC-16SM-806-618-APE

---

**Twist Test Method** FOTP-85

## Optical Specifications

**Fiber Type** G.657.A2/B2 | G.657.A2/B2

## Environmental Specifications

**Installation temperature** -30 °C to +70 °C (-22 °F to +158 °F)

**Operating Temperature** -40 °C to +80 °C (-40 °F to +176 °F)

**Storage Temperature** -40 °C to +80 °C (-40 °F to +176 °F)

**Cable Qualification Standards** ANSI/ICEA S-87-640 | Telcordia GR-20 | Telcordia GR-409

**Environmental Space** Wireless installation

## Packaging and Weights

**Cable weight** 1,616.146 kg/km | 1086 lb/kft

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## Included Products

CS-8G-MP	-	Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G.657.A2, B2)
----------	---	--

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable