

Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser Distribution, 12 fiber single-unit, Multimode OM4, Feet jacket marking, Blue jacket color, Dca flame rating

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series N-DS

General Specifications

 Cable Type
 Distribution

Construction Type Non-armored

**Subunit Type** Gel-free

Jacket Color Blue

Jacket Marking Feet


Total Fiber Count 12

**Dimensions** 

**Diameter Over Jacket** 6.07 mm | 0.239 in

Representative Image





#### Mechanical Specifications

Minimum Bend Radius, loaded

Minimum Bend Radius, unloaded

Tensile Load, long term, maximum

Tensile Load, short term, maximum

Compression

**Compression Test Method** 

**Flex** 

Flex Test Method

Impact

**Impact Test Method** 

Strain

Strain Test Method

**Twist** 

**Twist Test Method** 

Vertical Rise, maximum

Optical Specifications

**Fiber Type** 

91 mm | 3.583 in

61 mm | 2.402 in

200 N | 44.962 lbf

667 N | 149.948 lbf

10 N/mm | 57.101 lb/in

FOTP-41 | IEC 60794-1 E3

100 cycles

FOTP-104 | IEC 60794-1 E6

2.94 N-m | 26.021 in lb

FOTP-25 | IEC 60794-1 E4

See long and short term tensile loads

FOTP-33 | IEC 60794-1 E1

10 cycles

FOTP-85 | IEC 60794-1 E7

500 m | 1,640.42 ft

OM4, LazrSPEED® 550 | OM4, LazrSPEED® 550

**COMMSCOPE®** 

#### **Environmental Specifications**

Installation temperature  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  ( $+14 \,^{\circ}\text{F}$  to  $+140 \,^{\circ}\text{F}$ )

**Operating Temperature**  $-20 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \left(-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F}\right)$ 

**Storage Temperature**  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceDcaEN50575 CPR Cable EuroClass Smoke Rating\$1aEN50575 CPR Cable EuroClass Droplets Ratingd1EN50575 CPR Cable EuroClass Acidity Ratinga2

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL 1666 | UL 1685

**Environmental Test Specifications** 

**Heat Age** -20 °C to +85 °C (-4 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

**Low High Bend**  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $-20 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-4  $^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 34 kg/km | 22.847 lb/kft

#### Regulatory Compliance/Certifications

#### Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





#### Included Products

CS-5K-TB – LazrSPEED® 550 OM4 Bend-Insensitive Multimode

Fiber

#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable



#### LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber

#### LazrSPEED® 550

#### **Product Classification**

Portfolio CommScope®
Product Type Optical fiber

#### General Specifications

**Cladding Diameter** 125 µm **Cladding Diameter Tolerance** ±0.8 µm Cladding Non-Circularity, maximum 1 % **Coating Diameter (Colored)**  $254 \, \mu m$ **Coating Diameter (Uncolored)** 245 µm **Coating Diameter Tolerance (Colored)** ±7 µm **Coating Diameter Tolerance (Uncolored)** ±10 μm Coating/Cladding Concentricity Error, maximum 12 µm **Core Diameter** 50 µm **Core Diameter Tolerance** ±2.5 µm

**Proof Test** 689.476 N/mm² | 100000 psi

Tight Buffer Diameter 900  $\mu m$ Tight Buffer Diameter Tolerance  $\pm 40 \ \mu m$ 

### Mechanical Specifications

Core/Clad Offset, maximum

 Macrobending, 15 mm Ø mandrel, 2 turns
 0.20 dB @ 850 nm | 0.50 dB @ 1,300 nm

 Macrobending, 30 mm Ø mandrel, 2 turns
 0.10 dB @ 850 nm | 0.30 dB @ 1,300 nm

 Macrobending, 75 mm Ø mandrel, 100 turns
 0.50 dB @ 1,300 nm | 0.50 dB @ 850 nm

 $1.5 \, \mu m$ 

Coating Strip Force, maximum 8.9 N | 2.001 lbf

**COMMSCOPE®** 

### CS-5K-TB

Coating Strip Force, minimum 1.3 N | 0.292 lbf

**Dynamic Fatigue Parameter, minimum** 18

**Optical Specifications** 

Numerical Aperture 0.2

Numerical Aperture Tolerance±0.015Point Defects, maximum0.15 dB

**Zero Dispersion Slope, maximum** 0.105 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1316 nmZero Dispersion Wavelength, minimum1297 nm

Optical Specifications, Wavelength Specific

**1 Gbps Ethernet Distance** 1,110 m @ 850 nm | 600 m @ 1,300 nm

**10 Gbps Ethernet Distance** 550 m @ 850 nm

**Attenuation, maximum** 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

**Backscatter Coefficient** -68.0 dB @ 850 nm | -75.7 dB @ 1,300 nm

 Bandwidth, Laser, minimum
 4,700 MHz-km @ 850 nm | 500 MHz-km @ 1,300 nm

 Bandwidth, OFL, minimum
 3,500 MHz-km @ 850 nm | 500 MHz-km @ 1,300 nm

**Differential Mode Delay** 0.70 ps/m @ 850 nm

Differential Mode Delay Note Superior to ANSI/TIA TIA-492AAAF and IEC 60793-2-10 at 850 nm

**Index of Refraction** 1.479 @ 1,300 nm | 1.483 @ 850 nm

**Standards Compliance** ANSI/TIA-492AAAF (OM4) | IEC 60793-2-10, A1 (OM4)

**Environmental Specifications** 

**Heat Aging, maximum** 0.20 dB/km @ 85 °C

Temperature Dependence, maximum0.1 dB/kmTemperature Humidity Cycling, maximum0.2 dB/km

**Water Immersion, maximum** 0.20 dB/km @ 23 °C

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

\* Footnotes

**COMMSCOPE®** 

# CS-5K-TB

**Temperature Dependence, maximum** 

Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity