


# 760245035 | P-144-MZ-8G1-F12YL



Fiber indoor cable, Plenum MPO Trunk, interlocking aluminum armored with plenum jacket, 144 fiber multi-unit with 12 fiber subunits, Gel-free, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color

## Product Classification

|                       |  |
|-----------------------|--|
| Regional Availability | Asia   Australia/New Zealand   Latin America   Middle East /Africa   North America |
| Portfolio             | CommScope®   |
| Product Type          | Fiber indoor cable   |
| Product Series        | P-MZ   |

## General Specifications

|                              |                       |
|------------------------------|-----------------------|
| Armor Type                   | Interlocking aluminum |
| Cable Type                   | MPO trunk cable       |
| Construction Type            | Armored               |
| Subunit Type                 | Gel-free              |
| Jacket Color                 | Yellow                |
| Jacket Marking               | Feet                  |
| Subunit, quantity            | 12                    |
| Fibers per Subunit, quantity | 12                    |
| Total Fiber Count            | 144                   |

## Dimensions

|                              |                     |
|------------------------------|---------------------|
| Buffer Tube/Subunit Diameter | 3 mm   0.118 in     |
| Diameter Over Armor          | 20.96 mm   0.825 in |
| Diameter Over Jacket         | 23 mm   0.906 in    |

## Representative Image



## Mechanical Specifications

|                                   |                                       |
|-----------------------------------|---------------------------------------|
| Minimum Bend Radius, loaded       | 345 mm   13.583 in                    |
| Minimum Bend Radius, unloaded     | 230 mm   9.055 in                     |
| Tensile Load, long term, maximum  | 400 N   89.924 lbf                    |
| Tensile Load, short term, maximum | 1335 N   300.12 lbf                   |
| Compression                       | 85 N/mm   485.363 lb/in               |
| Compression Test Method           | FOTP-41   IEC 60794-1 E3              |
| Flex                              | 300 cycles                            |
| Flex Test Method                  | FOTP-104   IEC 60794-1 E6             |
| Impact                            | 35 N-m   309.776 in lb                |
| Impact Test Method                | FOTP-25   IEC 60794-1 E4              |
| Strain                            | See long and short term tensile loads |
| Strain Test Method                | FOTP-33   IEC 60794-1 E1              |
| Twist                             | 10 cycles                             |
| Twist Test Method                 | FOTP-85   IEC 60794-1 E7              |
| Vertical Rise, maximum            | 104 m   341.207 ft                    |

## Optical Specifications

|            |                           |
|------------|---------------------------|
| Fiber Type | G.657.A2/B2   G.657.A2/B2 |
|------------|---------------------------|

## Environmental Specifications

|                          |                                    |
|--------------------------|------------------------------------|
| Installation temperature | 0 °C to +70 °C (+32 °F to +158 °F) |
|--------------------------|------------------------------------|

# 760245035 | P-144-MZ-8G1-F12YL

|                               |                                       |
|-------------------------------|---------------------------------------|
| Operating Temperature         | 0 °C to +70 °C (+32 °F to +158 °F)    |
| Storage Temperature           | -40 °C to +70 °C (-40 °F to +158 °F)  |
| Cable Qualification Standards | ANSI/ICEA S-83-596   Telcordia GR-409 |
| Environmental Space           | Plenum                                |
| Flame Test Listing            | NEC OFCP (ETL) and c(ETL)             |
| Flame Test Method             | NFPA 130   NFPA 262                   |

## Environmental Test Specifications

|                               |                                    |
|-------------------------------|------------------------------------|
| Heat Age                      | 0 °C to +85 °C (+32 °F to +185 °F) |
| Heat Age Test Method          | IEC 60794-1 F9                     |
| Low High Bend                 | 0 °C to +70 °C (+32 °F to +158 °F) |
| Low High Bend Test Method     | FOTP-37   IEC 60794-1 E11          |
| Temperature Cycle             | 0 °C to +70 °C (+32 °F to +158 °F) |
| Temperature Cycle Test Method | FOTP-3   IEC 60794-1 F1            |

## Packaging and Weights

|              |                            |
|--------------|----------------------------|
| Cable weight | 392 kg/km   263.412 lb/kft |
|--------------|----------------------------|

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |



## Included Products

|           |   |  |
|-----------|---|--|
| CS-8G1-MP | – | Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G.657.A2, B2) |
|-----------|---|--|

## \* Footnotes

|                       |   |
|-----------------------|---|
| Operating Temperature | Specification applicable to non-terminated bulk fiber cable |
|-----------------------|---|

# CS-8G1-MP

Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G. 657.A2, B2)

## Product Classification

|              |               |
|--------------|---------------|
| Portfolio    | CommScope®    |
| Product Type | Optical fiber |

## General Specifications

|   |                            |
|---|----------------------------|
| Cladding Diameter                             | 125 µm                     |
| Cladding Diameter Tolerance                   | ±0.3 µm                    |
| Cladding Non-Circularity, maximum             | 0.7 %                      |
| Coating Diameter (Colored)                    | 249 µm                     |
| Coating Diameter (Uncolored)                  | 242 µm                     |
| Coating Diameter Tolerance (Colored)          | ±13 µm                     |
| Coating Diameter Tolerance (Uncolored)        | ±5 µm                      |
| Coating/Cladding Concentricity Error, maximum | 12 µm                      |
| Core/Clad Offset, maximum                     | 0.5 µm                     |
| Proof Test                                    | 689.476 N/mm²   100000 psi |

## Dimensions

|                     |                 |
|---------------------|-----------------|
| Fiber Curl, minimum | 4 m   13.123 ft |
|---------------------|-----------------|

## Mechanical Specifications

|   |   |
|---|---|
| Macrobending, 15 mm Ø mandrel, 1 turn   | 0.50 dB @ 1,550 nm   1.00 dB @ 1,625 nm |
| Macrobending, 20 mm Ø mandrel, 1 turn   | 0.10 dB @ 1,550 nm   0.20 dB @ 1,625 nm |
| Macrobending, 30 mm Ø mandrel, 10 turns | 0.03 dB @ 1,550 nm   0.10 dB @ 1,625 nm |
| Coating Strip Force, maximum            | 8.9 N   2.001 lbf                       |
| Coating Strip Force, minimum            | 1.3 N   0.292 lbf                       |
| Dynamic Fatigue Parameter, minimum      | 20                                      |

## Optical Specifications

|                                   |         |
|-----------------------------------|---------|
| Cabled Cutoff Wavelength, maximum | 1260 nm |
| Point Defects, maximum            | 0.1 dB  |

# CS-8G1-MP

|   |   |
|---|---|
| Zero Dispersion Slope, maximum                          | 0.092 ps/[km-nm-nm]   |
| Zero Dispersion Wavelength, maximum                     | 1324 nm   |
| Zero Dispersion Wavelength, minimum                     | 1302 nm   |
| Optical Specifications, Wavelength Specific             |   |
| Attenuation, maximum                                    | 0.40 dB/km @ 1,310 nm   0.40 dB/km @ 1,385 nm   0.40 dB/km @ 1,550 nm   0.50 dB/km @ 1,625 nm |
| Dispersion, maximum                                     | 18 ps(nm-km) at 1550 nm   3.5 ps(nm-km) from 1285 nm to 1330 nm at 1310 nm                    |
| Index of Refraction                                     | 1.467 @ 1,310 nm   1.467 @ 1,385 nm   1.468 @ 1,550 nm  |
| Mode Field Diameter                                     | 8.6 µm @ 1,310 nm   9.8 µm @ 1,550 nm   |
| Mode Field Diameter Tolerance                           | ±0.4 µm @ 1310 nm   ±0.5 µm @ 1550 nm   |
| Polarization Mode Dispersion Link Design Value, maximum | 0.06 ps/sqrt(km)  |
| Standards Compliance                                    | ITU-T G.657.A2   ITU-T G.657.B2   |

## Environmental Specifications

|                                       |                    |
|---------------------------------------|--------------------|
| Heat Aging, maximum                   | 0.05 dB/km @ 85 °C |
| Temperature Dependence, maximum       | 0.05 dB/km         |
| Temperature Humidity Cycling, maximum | 0.05 dB/km         |
| Water Immersion, maximum              | 0.05 dB/km @ 23 °C |

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

## \* Footnotes

|                                       |   |
|---------------------------------------|---|
| Temperature Dependence, maximum       | Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)                                   |
| Temperature Humidity Cycling, maximum | Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity |