R-008-DS-6F-FSU

Fiber indoor cable, OptiSPEED® Riser Distribution, 8 fiber single-unit, Multimode OM1, Feet jacket marking

Product Classification

Regional Availability	Asia | Australia/New Zealand | Latin America | Middle East/Africa | North America
Portfolio	CommScope®
Product Type	Fiber indoor cable
Product Series	R-DS

General Specifications

Cable Type	Distribution
Construction Type	Non-armored
Subunit Type	Gel-free
Jacket Marking	Feet
Total Fiber Count	8

Dimensions

Diameter Over Jacket	5.42 mm | 0.213 in

Representative Image



Mechanical Specifications

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025

Minimum Bend Radius, loaded	81 mm | 3.189 in
Minimum Bend Radius, unloaded	54 mm | 2.126 in
Tensile Load, long term, maximum	200 N | 44.962 lbf
Tensile Load, short term, maximum	667 N | 149.948 lbf
Compression	10 N/mm | 57.101 lb/in
Compression Test Method	FOTP-41 | IEC 60794-1 E3
Flex	100 cycles
Flex Test Method	FOTP-104 | IEC 60794-1 E6
Impact	2.94 N-m | 26.021 in lb
Impact Test Method	FOTP-25 | IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33 | IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85 | IEC 60794-1 E7
Vertical Rise, maximum	500 m | 1,640.42 ft

Optical Specifications

Fiber Type	OM1, OptiSPEED® | OM1, OptiSPEED®

Environmental Specifications

Installation temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Cable Qualification Standards	ANSI/ICEA S-83-596 | Telcordia GR-409
Environmental Space	Riser
Flame Test Listing	NEC OFNR (ETL) and c(ETL)
Flame Test Method	UL 1666

Environmental Test Specifications

Heat Age	-20 °C to +85 °C (-4 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	-20 °C to +70 °C (-4 °F to +158 °F)
Low High Bend Test Method	FOTP-37 | IEC 60794-1 E11

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025

COMMSCOPE®

Temperature Cycle	-20 °C to +70 °C (-4 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight	26 kg/km | 17.471 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Included Products

CS-6F-TB – OptiSPEED® OM1 Multimode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025

OptiSPEED®

OptiSPEED® OM1 Multimode Fiber

Product Classification

Portfolio	CommScope®
Product Type	Optical fiber

General Specifications

Cladding Diameter	125 µm
Cladding Diameter Tolerance	±1.0 µm
Cladding Non-Circularity, maximum	1 %
Coating Diameter (Colored)	254 µm
Coating Diameter (Uncolored)	245 µm
Coating Diameter Tolerance (Colored)	±7 µm
Coating Diameter Tolerance (Uncolored)	±10 µm
Coating/Cladding Concentricity Error, maximum	12 µm
Core Diameter	62.5 µm
Core Diameter Tolerance	±2.5 µm
Core/Clad Offset, maximum	1 µm
Proof Tensile Stress	100,000 psi (0.69 GPa)
Tight Buffer Diameter	900 µm
Tight Buffer Diameter Tolerance	±40 µm

Mechanical Specifications

Macrobending, 75 mm Ø mandrel, 100 turns	0.50 dB @ 1,300 nm | 0.50 dB @ 850 nm
Coating Strip Force, maximum	8.9 N | 2.001 lbf
Coating Strip Force, minimum	1.3 N | 0.292 lbf
Dynamic Fatigue Parameter, minimum	18

Optical Specifications

Numerical Aperture	0.275

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 30, 2025

COMMSCOPE®

Numerical Aperture Tolerance	±0.015
Point Defects, maximum	0.15 dB
Zero Dispersion Slope, maximum	0.097 ps/[km-nm-nm]
Zero Dispersion Wavelength, maximum	1365 nm
Zero Dispersion Wavelength, minimum	1320 nm

Optical Specifications, Wavelength Specific

1 Gbps Ethernet Distance	300 m @ 850 nm | 550 m @ 1,300 nm
Attenuation, maximum	1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm
Backscatter Coefficient	-68.0 dB @ 850 nm | -75.7 dB @ 1,300 nm
Bandwidth, OFL, minimum	220 MHz-km @ 850 nm | 500 MHz-km @ 1,300 nm
Index of Refraction	1.491 @ 1,300 nm | 1.496 @ 850 nm
Standards Compliance	TIA-492AAAA (OM1)

Environmental Specifications

Heat Aging, maximum	0.20 dB/km @ 85 °C
Temperature Dependence, maximum	0.1 dB/km
Temperature Humidity Cycling, maximum	0.2 dB/km
Water Immersion, maximum	0.20 dB/km @ 23 °C

Regulatory Compliance/Certifications

Agency	**Classification**
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Temperature Dependence, maximum	Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)
Temperature Humidity Cycling, maximum	Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 30, 2025