

# R-060-DS-8W-FMU

Fiber indoor cable, TeraSPEED® Riser Distribution 60 fiber Multi-Unit with 12-Fiber Subunits, Singlemode G.652.D and G.657.A1, Feet jacket marking

## Product Classification

Regional Availability	Asia   Australia/New Zealand   Latin America   Middle East /Africa   North America
Portfolio	CommScope®
Product Type	Fiber indoor cable
Product Series	R-DS


## General Specifications

Cable Type	Distribution
Construction Type	Non-armored
Subunit Type	Gel-free
Jacket Marking	Feet
Subunit, quantity	5
Fibers per Subunit, quantity	12
Total Fiber Count	60

## Dimensions

Buffer Tube/Subunit Diameter	5.95 mm   0.234 in
Diameter Over Jacket	17.88 mm   0.704 in

## Representative Image



# R-060-DS-8W-FMU

## Mechanical Specifications

Minimum Bend Radius, loaded	268 mm   10.551 in
Minimum Bend Radius, unloaded	179 mm   7.047 in
Tensile Load, long term, maximum	400 N   89.924 lbf
Tensile Load, short term, maximum	1335 N   300.12 lbf
Compression	10 N/mm   57.101 lb/in
Compression Test Method	FOTP-41   IEC 60794-1 E3
Flex	100 cycles
Flex Test Method	FOTP-104   IEC 60794-1 E6
Impact	5.88 N-m   52.042 in lb
Impact Test Method	FOTP-25   IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33   IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85   IEC 60794-1 E7
Vertical Rise, maximum	146 m   479.003 ft

## Optical Specifications

Fiber Type	G.652.D and G.657.A1, TeraSPEED®
------------	----------------------------------

## Environmental Specifications

Installation temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Cable Qualification Standards	ANSI/ICEA S-83-596   Telcordia GR-409
Environmental Space	Riser
Flame Test Listing	NEC OFNR (ETL) and c(ETL)
Flame Test Method	UL 1666

## Environmental Test Specifications

Heat Age	-20 °C to +85 °C (-4 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9

# R-060-DS-8W-FMU

---

Low High Bend	-20 °C to +70 °C (-4 °F to +158 °F)
Low High Bend Test Method	FOTP-37   IEC 60794-1 E11
Temperature Cycle	-20 °C to +70 °C (-4 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3   IEC 60794-1 F1

## Packaging and Weights

Cable weight	279 kg/km   187.479 lb/kft
--------------	----------------------------

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## Included Products

CS-8W-TB – TeraSPEED® Singlemode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable