# 760009340 | N-072-DS-CM-FMUAQ/8W012 /5L060



Fiber indoor cable, TeraSPEED® Low Smoke Zero Halogen Riser Distribution, 72 fiber multi-unit with 12 fiber subunits, Gel-free, Singlemode + Multimode OM3, Feet jacket marking, Aqua jacket color

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series N-DS

General Specifications

 Cable Type
 Distribution

Construction Type Non-armored

**Subunit Type** Gel-free

Jacket Color Aqua

**Jacket Marking** Feet

Subunit, quantity 6

Fibers per Subunit, quantity 12

Composite Fiber Count 12 + 60

Total Fiber Count 72

Dimensions


**Buffer Tube/Subunit Diameter** 6.07 mm | 0.239 in

**Diameter Over Jacket** 20.01 mm | 0.788 in

Representative Image



# 760009340 | N-072-DS-CM-FMUAQ/8W012 /5L060



## Mechanical Specifications

Minimum Bend Radius, loaded 300 mm | 11.811 in

Minimum Bend Radius, unloaded 200 mm | 7.874 in

Tensile Load, long term, maximum 400 N | 89.924 lbf

Tensile Load, short term, maximum 1335 N | 300.12 lbf

**Compression** 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 100 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 5.88 N-m | 52.042 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 113 m | 370.735 ft

**Optical Specifications** 

Fiber Type Composite MM/SM | G.652.D and G.657.A1, TeraSPEED® | OM3,

LazrSPEED® 300

**Environmental Specifications** 

Installation temperature  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  ( $+14 \,^{\circ}\text{F}$  to  $+140 \,^{\circ}\text{F}$ )

Page 2 of 9

# 760009340 | N-072-DS-CM-FMUAQ/8W012 /5L060

Operating Temperature  $-20 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C } (-4 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F})$ Storage Temperature  $-40 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C } (-40 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F})$ 

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL 1666 | UL 1685

**Environmental Test Specifications** 

**Heat Age**  $-20 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$   $(-4 \,^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F})$ 

**Heat Age Test Method** IEC 60794-1 F9

**Low High Bend** -10 °C to +60 °C (+14 °F to +140 °F)

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $-20 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 360 kg/km | 241.909 lb/kft

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



#### Included Products

CS-5L-TB – LazrSPEED® 300 OM3 Bend-Insensitive Multimode

Fiber

CS-8W-TB – TeraSPEED® Singlemode Fiber

#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable



### LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber

## LazrSPEED® 300

### **Product Classification**

Portfolio CommScope®
Product Type Optical fiber

## General Specifications

**Cladding Diameter** 125 µm **Cladding Diameter Tolerance** ±0.8 µm Cladding Non-Circularity, maximum 1 % **Coating Diameter (Colored)**  $254 \, \mu m$ **Coating Diameter (Uncolored)** 245 µm **Coating Diameter Tolerance (Colored)** ±7 µm **Coating Diameter Tolerance (Uncolored)** ±10 μm Coating/Cladding Concentricity Error, maximum 12 µm **Core Diameter** 50 µm **Core Diameter Tolerance** ±2.5 µm

**Proof Test** 689.476 N/mm<sup>2</sup> | 100000 psi

Tight Buffer Diameter 900  $\mu m$ Tight Buffer Diameter Tolerance  $\pm 40 \ \mu m$ 

## Mechanical Specifications

Core/Clad Offset, maximum

 Macrobending, 15 mm Ø mandrel, 2 turns
 0.20 dB @ 850 nm | 0.50 dB @ 1,300 nm

 Macrobending, 30 mm Ø mandrel, 2 turns
 0.10 dB @ 850 nm | 0.30 dB @ 1,300 nm

 Macrobending, 75 mm Ø mandrel, 100 turns
 0.50 dB @ 1,300 nm | 0.50 dB @ 850 nm

 $1.5 \, \mu m$ 

Coating Strip Force, maximum 8.9 N | 2.001 lbf



## CS-5L-TB

Coating Strip Force, minimum 1.3 N | 0.292 lbf

**Dynamic Fatigue Parameter, minimum** 18

**Optical Specifications** 

Numerical Aperture 0.2

Numerical Aperture Tolerance ±0.015

Point Defects, maximum 0.15 dB

**Zero Dispersion Slope, maximum** 0.105 ps/[km-nm-nm]

**Zero Dispersion Wavelength, maximum** 1316 nm **Zero Dispersion Wavelength, minimum** 1297 nm

Optical Specifications, Wavelength Specific

**1 Gbps Ethernet Distance** 1,020 m @ 850 nm | 600 m @ 1,300 nm

**10 Gbps Ethernet Distance** 300 m @ 850 nm

**Attenuation, maximum** 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

**Backscatter Coefficient** -68.0 dB @ 850 nm | -75.7 dB @ 1,300 nm

 Bandwidth, Laser, minimum
 2,000 MHz-km @ 850 nm | 500 MHz-km @ 1,300 nm

 Bandwidth, OFL, minimum
 1,500 MHz-km @ 850 nm | 500 MHz-km @ 1,300 nm

**Differential Mode Delay** 0.70 ps/m @ 850 nm

Differential Mode Delay Note Superior to ANSI/TIA TIA-492AAAF and IEC 60793-2-10 at 850 nm

**Index of Refraction** 1.479 @ 1,300 nm | 1.483 @ 850 nm

Standards Compliance ANSI/TIA-492AAAF (OM3)

**Environmental Specifications** 

**Heat Aging, maximum** 0.20 dB/km @ 85 °C

Temperature Dependence, maximum0.1 dB/kmTemperature Humidity Cycling, maximum0.2 dB/km

**Water Immersion, maximum** 0.20 dB/km @ 23 °C

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

\* Footnotes

**COMMSCOPE®** 

# CS-5L-TB

**Temperature Dependence, maximum** 

Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity

Page 6 of 9

## TeraSPEED® Singlemode Fiber

## TeraSPEED®

### **Product Classification**

 Portfolio
 CommScope®

 Product Type
 Optical fiber

## General Specifications

**Cladding Diameter** 125 µm **Cladding Diameter Tolerance**  $\pm 0.7 \, \mu m$ Cladding Non-Circularity, maximum 0.7 % **Coating Diameter (Colored)** 249 µm **Coating Diameter (Uncolored)** 242 µm **Coating Diameter Tolerance (Colored)** ±13 μm **Coating Diameter Tolerance (Uncolored)** ±5 µm Coating/Cladding Concentricity Error, maximum 12 µm **Core Diameter** 8.3 µm Core/Clad Offset, maximum  $0.5 \, \mu m$ 

**Proof Test** 689.476 N/mm² | 100000 psi

Tight Buffer Diameter 900  $\mu m$ Tight Buffer Diameter Tolerance  $\pm 40 \ \mu m$ 

#### **Dimensions**

Fiber Curl, minimum 4 m | 13.123 ft

### Mechanical Specifications

 Macrobending, 20 mm Ø mandrel, 1 turn
 0.75 dB @ 1,550 nm | 1.50 dB @ 1,625 nm

 Macrobending, 30 mm Ø mandrel, 10 turns
 0.25 dB @ 1,550 nm | 1.00 dB @ 1,625 nm

**COMMSCOPE®** 

## CS-8W-TB

**Macrobending, 60 mm Ø mandrel, 100 turns** 0.05 dB @ 1,550 nm | 0.05 dB @ 1,625 nm

Coating Strip Force, maximum8.9 N | 2.001 lbfCoating Strip Force, minimum1.3 N | 0.292 lbf

Dynamic Fatigue Parameter, minimum 20

**Optical Specifications** 

Cabled Cutoff Wavelength, maximum1260 nmPoint Defects, maximum0.1 dB

**Zero Dispersion Slope, maximum** 0.092 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1324 nmZero Dispersion Wavelength, minimum1300 nm

Optical Specifications, Wavelength Specific

**Attenuation, maximum** 0.50 dB/km @ 1,310 nm | 0.50 dB/km @ 1,385

nm | 0.50 dB/km @ 1,490 nm | 0.50 dB/km @ 1,550 nm | 0.50 dB/km @ 1,575 nm | 0.70 dB/km @ 1,270

nm

**Backscatter Coefficient** -79.6 dB @ 1,310 nm | -82.1 dB @ 1,550 nm

**Dispersion, maximum** 18 ps(nm-km) at 1550 nm | 3.5 ps(nm-km) from 1285

nm to 1330 nm at 1310 nm

Index of Refraction 1.467 @ 1,310 nm | 1.467 @ 1,385 nm | 1.468 @ 1,550

nm

1,385 nm

**Mode Field Diameter Tolerance** ±0.4 μm @ 1310 nm | ±0.5 μm @ 1550 nm | ±0.6 μm

@ 1385 nm

**Polarization Mode Dispersion Link Design Value, maximum** 0.04 ps/sqrt(km)

Standards Compliance | ITU-T G.652.D | ITU-T G.657.A1 | TIA-492CAAB (OS1a)

**Environmental Specifications** 

Heat Aging, maximum 0.05 dB/km @ 85 °C

 Temperature Dependence, maximum
 0.05 dB/km

 Temperature Humidity Cycling, maximum
 0.05 dB/km

Water Immersion, maximum 0.05 dB/km @ 23 °C

Regulatory Compliance/Certifications

COMMSC PE°

## CS-8W-TB

#### Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

### \* Footnotes

**Temperature Dependence, maximum** Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

**Temperature Humidity Cycling, maximum** Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

