
760018879 | P-144-DS-5L-FMUAQ



Fiber indoor cable, LazrSPEED® Plenum Distribution, 144 fiber multi-unit with 12 fiber subunits, Multimode OM3, Feet jacket marking, Aqua jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series P-DS

General Specifications

Cable TypeDistribution

Construction Type Non-armored

Subunit Type Gel-free

Jacket Color Aqua

Jacket Marking Feet

Subunit, quantity 12

Fibers per Subunit, quantity 12

Total Fiber Count 144

Dimensions


Buffer Tube/Subunit Diameter 5.77 mm | 0.227 in

Diameter Over Jacket 24.41 mm | 0.961 in

Representative Image



760018879 | P-144-DS-5L-FMUAQ



Mechanical Specifications

Minimum Bend Radius, loaded 366 mm | 14.409 in

Minimum Bend Radius, unloaded 244 mm | 9.606 in

Tensile Load, long term, maximum 400 N | 89.924 lbf

Tensile Load, short term, maximum 1335 N | 300.12 lbf

Compression 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 100 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 5.88 N-m | 52.042 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 77 m | 252.625 ft

Optical Specifications

Fiber Type OM3, LazrSPEED® 300 | OM3, LazrSPEED® 300

Environmental Specifications

Installation temperature 0 °C to +70 °C (+32 °F to +158 °F)

COMMSCOPE®

760018879 | P-144-DS-5L-FMUAQ

Operating Temperature $-20 \, ^{\circ}\text{C} \text{ to } +70 \, ^{\circ}\text{C} \, (-4 \, ^{\circ}\text{F to } +158 \, ^{\circ}\text{F})$

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing

NEC OFNP (ETL) and c(ETL)

Flame Test Method

NFPA 130 | NFPA 262

Environmental Test Specifications

Heat Age $-20 \, ^{\circ}\text{C} \text{ to } +85 \, ^{\circ}\text{C} \, (-4 \, ^{\circ}\text{F to } +185 \, ^{\circ}\text{F})$

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-20 \, ^{\circ}\text{C} \text{ to } +70 \, ^{\circ}\text{C} \, (-4 \, ^{\circ}\text{F to } +158 \, ^{\circ}\text{F})$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle $-20 \,^{\circ}\text{C to} +70 \,^{\circ}\text{C} \left(-4 \,^{\circ}\text{F to} +158 \,^{\circ}\text{F}\right)$

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 531 kg/km | 356.816 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

CS-5L-TB – LazrSPEED® 300 OM3 Bend-Insensitive Multimode

Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

