
760038364 | P-024-MP-6F-F12SL



Fiber indoor cable, OptiSPEED® Plenum MPO Trunk, 24 fiber with 12 fiber subunits, Multimode OM1, Feet jacket marking, Slate jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series P-MP

General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored

Subunit Type Gel-free

Jacket Color Slate

Jacket Marking Feet

Subunit, quantity 2

Fibers per Subunit, quantity 12

Total Fiber Count 24


Dimensions

Height Over Jacket3.9 mm0.154 inWidth Over Jacket6.9 mm0.272 inBuffer Tube/Subunit Diameter3 mm0.118 in

Representative Image



760038364 | P-024-MP-6F-F12SL



Mechanical Specifications

Minimum Bend Radius, loaded58 mm | 2.283 inMinimum Bend Radius, unloaded39 mm | 1.535 inTensile Load, long term, maximum200 N | 44.962 lbfTensile Load, short term, maximum667 N | 149.948 lbf

 Compression
 10 N/mm | 57.101 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 500 m | 1,640.42 ft

Optical Specifications

Fiber Type OM1, OptiSPEED® | OM1, OptiSPEED®

Environmental Specifications

Installation temperature 0 °C to +70 °C (+32 °F to +158 °F)

Page 2 of 5

760038364 | P-024-MP-6F-F12SL

Operating Temperature 0 °C to +70 °C (+32 °F to +158 °F)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing NEC OFNP (ETL) and c(ETL)

Flame Test Method NFPA 130 | NFPA 262

Environmental Test Specifications

Heat Age 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend $0 \degree \text{C to } +70 \degree \text{C (} +32 \degree \text{F to } +158 \degree \text{F)}$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle 0 °C to +70 °C (+32 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 29 kg/km | 19.487 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant UK-ROHS Compliant



Included Products

CS-6F-MP - OptiSPEED® OM1 Multimode

Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



OptiSPEED®

OptiSPEED® OM1 Multimode Fiber

Product Classification

 Portfolio
 CommScope®

 Product Type
 Optical fiber

General Specifications

Cladding Diameter 125 µm **Cladding Diameter Tolerance** ±1.0 µm Cladding Non-Circularity, maximum 1 % **Coating Diameter (Colored)** 254 µm **Coating Diameter (Uncolored)** 245 µm **Coating Diameter Tolerance (Colored)** ±7 µm **Coating Diameter Tolerance (Uncolored)** ±10 µm Coating/Cladding Concentricity Error, maximum 12 µm **Core Diameter** 62.5 µm **Core Diameter Tolerance** ±2.5 µm

Proof Test 689.476 N/mm² | 100000 psi

Mechanical Specifications

Core/Clad Offset, maximum

Macrobending, 75 mm Ø mandrel, 100 turns 0.50 dB @ 1,300 nm | 0.50 dB @ 850 nm

1 µm

Coating Strip Force, maximum8.9 N | 2.001 lbfCoating Strip Force, minimum1.3 N | 0.292 lbf

Dynamic Fatigue Parameter, minimum 18

Optical Specifications

Numerical Aperture0.275Numerical Aperture Tolerance±0.015Point Defects, maximum0.15 dB

Page 4 of 5



CS-6F-MP

Zero Dispersion Slope, maximum 0.097 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum 1365 nm **Zero Dispersion Wavelength, minimum** 1320 nm

Optical Specifications, Wavelength Specific

1 Gbps Ethernet Distance 300 m @ 850 nm | 550 m @ 1,300 nm

Attenuation, maximum 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

Backscatter Coefficient -68.0 dB @ 850 nm | -75.7 dB @ 1,300 nm

Bandwidth, OFL, minimum 220 MHz-km @ 850 nm | 500 MHz-km @ 1,300 nm

Index of Refraction 1.491 @ 1,300 nm | 1.496 @ 850 nm

Standards Compliance TIA-492AAAA (OM1)

Environmental Specifications

Heat Aging, maximum 0.20 dB/km @ 85 °C

Temperature Dependence, maximum0.1 dB/kmTemperature Humidity Cycling, maximum0.2 dB/km

Water Immersion, maximum 0.20 dB/km @ 23 °C

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Temperature Dependence, maximum Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

