

Indoor/Outdoor Fiber Optic Cable, Dry, 12-fiber, OFNR, OM4, black

Product Classification

| | |
|-----------------------|--------------------------------------|
| Regional Availability | Asia Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber indoor/outdoor cable |
| Product Series | C-DS |

General Specifications

| | |
|------------------------------|------------|
| Cable Type | Loose tube |
| Subunit Type | Gel-free |
| Jacket Color | Black |
| Jacket Marking | Meters |
| Fibers per Subunit, quantity | 12 |
| Total Fiber Count | 12 |

Dimensions

| | |
|----------------------|-------------------|
| Diameter Over Jacket | 7.3 mm 0.287 in |
|----------------------|-------------------|

Mechanical Specifications

| | |
|-----------------------------------|----------------------|
| Minimum Bend Radius, loaded | 149.9 mm 5.902 in |
| Minimum Bend Radius, unloaded | 75 mm 2.953 in |
| Tensile Load, long term, maximum | 400 N 89.924 lbf |
| Tensile Load, short term, maximum | 1334 N 299.895 lbf |

Optical Specifications

| | |
|------------|-----------------|
| Fiber Type | OM4, LazrSPEED® |
|------------|-----------------|

Optical Specifications, Wavelength Specific

| | |
|---------------------------|--|
| 10 Gbps Ethernet Distance | 550 m @ 850 nm |
| Attenuation, maximum | 1.00 dB/km @ 1,300 nm 3.20 dB/km @ 850 nm |
| Bandwidth, Laser, minimum | 4,700 MHz-km @ 850 nm |
| Bandwidth, OFL, minimum | 3,500 MHz-km @ 850 nm 500 MHz-km @ 1,300 nm |
| Standards Compliance | ANSI/TIA-568.B.1 ANSI/TIA-568.B.2 IEC 60793-2-10 TIA-492AAAD (OM4) |

Environmental Specifications

| | |
|--------------------------|--------------------------------------|
| Installation temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Operating Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Environmental Space | Riser |

Packaging and Weights

| | |
|--------------|--------------------------|
| Cable weight | 60 kg/km 40.318 lb/kft |
|--------------|--------------------------|

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |



* Footnotes

| | |
|-----------------------|---|
| Operating Temperature | Specification applicable to non-terminated bulk fiber cable |
|-----------------------|---|