

Fiber indoor cable, TeraSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 72 fiber multi-unit with 12 fiber subunits, Gel-free, Singlemode G. 652.D and G.657.A1, Feet jacket marking, Yellow jacket color, Dca flame rating

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series N-MP

General Specifications

Cable TypeMPO trunk cable

Construction Type Non-armored

Subunit Type Gel-free

Jacket Color Yellow

Jacket Marking Feet

Subunit, quantity 6

Fibers per Subunit, quantity 12

Total Fiber Count 72


Dimensions

Buffer Tube/Subunit Diameter 3 mm | 0.118 in

Diameter Over Jacket 10.75 mm | 0.423 in

Representative Image





Mechanical Specifications

Minimum Bend Radius, loaded161 mm6.339 inMinimum Bend Radius, unloaded107 mm4.213 in

Tensile Load, long term, maximum 400 N | 89.924 lbf

Tensile Load, short term, maximum 1335 N | 300.12 lbf

 Compression
 10 N/mm | 57.101 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 401 m | 1,315.617 ft

Optical Specifications

Fiber Type G.652.D and G.657.A1, TeraSPEED® | OS2 | OS2

Environmental Specifications

Installation temperature $-20 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Page 2 of 4

Operating Temperature $-20 \, ^{\circ}\text{C} \text{ to } +70 \, ^{\circ}\text{C} \, (-4 \, ^{\circ}\text{F to } +158 \, ^{\circ}\text{F})$

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire Performance Dca
EN50575 CPR Cable EuroClass Smoke Rating s1a
EN50575 CPR Cable EuroClass Droplets Rating d1
EN50575 CPR Cable EuroClass Acidity Rating a1

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL 1666 | UL 1685

Environmental Test Specifications

Heat Age $-20 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ $(-4 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F})$

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-20 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-4 °F to $+158 \,^{\circ}\text{F}$)Low High Bend Test MethodFOTP-37 | IEC 60794-1 E11Temperature Cycle $-20 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-4 °F to $+158 \,^{\circ}\text{F}$)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 102 kg/km | 68.541 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

CS-8W-MP - TeraSPEED® OS2 Singlemode

COMMSC PE®

Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable