


# CX3750001 | 200T040P3750JCASS COEX



ConQuest® Cable in Conduit, 2 in, SCH 40, terracotta (P3® 750 JCASS)

- \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

## Product Classification

Regional Availability	North America
Product Type	Coaxial cable-in-conduit
Product Brand	ConQuest®
Product Series	750 Series
Government Requirements	Build America Buy America (BABA) compliant*

## General Specifications

Cable Type	750 Series
Cable-In-Conduit Type	P3® in duct
Color	Terracotta
Conduit Type	Non-toneable
Location of Manufacturing	Catawba, North Carolina
Wall Type	Smooth

## Dimensions

Length	762 m   2500 ft
Wall Thickness Designation	SCH 40
Nominal Size	2 in

## Packaging and Weights

Weight, net	1,005.999 kg/km   676 lb/kft
-------------	------------------------------

## Included Products

5304203 P3® 750 JCASS	–	75 Ohm P3® Trunk and Distribution Cable, black PE jacket, flooded for underground
--------------------------	---	---

# CX3750001 | 200T040P3750JCASS COEX

---

CX3799999 – ConQuest® Empty Conduit, 2 in, SCH 40, terracotta  
200T040 EMPTY DUCT COEX



- \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

## Product Classification

Regional Availability	North America
Product Type	Coaxial hardline cable
Product Brand	P3®
Government Requirements	Build America Buy America (BABA) compliant*
Warranty	One year

## General Specifications

Cable Type	750 Series
Construction Type	Swaged
Jacket Color	Black
Location of Manufacturing	Catawba, North Carolina
Short Description	P3 750 JCASS SM PR997

## Dimensions

Cable Length	762 m   2500 ft
Diameter Over Center Conductor, nominal	4.242 mm   0.167 in
Diameter Over Dielectric, nominal	17.323 mm   0.682 in
Diameter Over Jacket, nominal	21.082 mm   0.83 in
Diameter Over Outer Conductor, nominal	19.05 mm   0.75 in
Jacket Thickness, nominal	0.889 mm   0.035 in
Outer Conductor Thickness, nominal	0.864 mm   0.034 in

## Electrical Specifications

Capacitance	50.197 pF/m   15.3 pF/ft
-------------	--------------------------

Capacitance Tolerance	±1.0 pF/ft
Characteristic Impedance	75 ohm
Characteristic Impedance Tolerance	±2 ohm
dc Resistance Note	Nominal values based on a standard condition of 20 °C (68 °F)
dc Resistance, Inner Conductor, nominal	1.87 ohms/km   0.57 ohms/kft
dc Resistance, Loop, nominal	2.493 ohms/km   0.76 ohms/kft
dc Resistance, Outer Conductor, nominal	0.623 ohms/km   0.19 ohms/kft
Jacket Spark Test Voltage	5000 Vac
Nominal Velocity of Propagation (NVP)	87 %
Operating Frequency Band	5–3000 MHz
Structural Return Loss	24 dB @ 1003–1218 MHz   24 dB @ 1219–1794 MHz   30 dB @ 5–1002 MHz
Structural Return Loss, Grade N	≥24 dB @ 1003–1218 MHz   ≥24 dB @ 1219–1794 MHz   ≥30 dB @ 5–1002 MHz

## Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5.0	0.36	0.11
55.0	1.21	0.37
85.0	1.51	0.46
204.0	2.36	0.72
211.0	2.43	0.74
250.0	2.66	0.81
300.0	2.92	0.89
350.0	3.18	0.97
400.0	3.44	1.05
450.0	3.67	1.12
500.0	3.87	1.18
550.0	4.07	1.24
600.0	4.3	1.31
750.0	4.86	1.48
865.0	5.28	1.61
1002.0	5.72	1.74
1218.0	6.41	1.95
1500.0	7.3	2.23

# 5304203 | P3® 750 JCASS

1794.0	8.07	2.46
1800.0	8.08	2.46
2000.0	8.57	2.61
2200.0	9.05	2.76
2500.0	9.73	2.96
2700.0	10.16	3.1
3000.0	10.8	3.29

## Material Specifications

Center Conductor Material	Copper-clad aluminum
Dielectric Material	Foam PE
Jacket Material	PE
Outer Conductor Material	Aluminum

## Mechanical Specifications

Minimum Bend Radius, bonded	152.4 mm   6 in
Pulling Tension, maximum	306.175 kg   675 lb

## Environmental Specifications

Corrosion Protection	Migraheal®
Environmental Space	Buried

## Packaging and Weights

Packaging Type	Reel
Weight, gross	398.828 kg/km   268 lb/kft


## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



CX37999999 | 200T040 EMPTY DUCT COEX

---



ConQuest® Empty Conduit, 2 in, SCH 40, terracotta

Product Classification

Product Type	Empty conduit
Product Brand	ConQuest®

General Specifications

Color	Terracotta
Conduit Type	Non-toneable
Density Test Method	ASTM D792A
Density, maximum	0.955 g/cm³   0.035 lb/in³
Density, minimum	0.941 g/cm³   0.034 lb/in³
Design Standard	ASTM D3350-05
Wall Type	Smooth

Dimensions

Length	762 m   2500 ft
Inner Diameter, nominal	51.994 mm   2.047 in
Outer Diameter, nominal	60.325 mm   2.375 in
Wall Thickness Designation	SCH 40
Wall Thickness, minimum	3.912 mm   0.154 in
Nominal Size	2 in

Material Specifications

Flexural Modulus, minimum	551.581 N/mm²   80000 psi
Flexural Property Test Method	ASTM D790
Hydrostatic Design Basis	Not pressure rated
Hydrostatic Design Test Method	ASTM D2837
Material Type	High density polyethylene (HDPE)
Melt Flow Rate Test Method	ASTM D1238

# CX37999999 | 200T040 EMPTY DUCT COEX

**Melt Flow Rate, maximum** 0.39 g/10 min

## Mechanical Specifications

**Minimum Bend Radius, unsupported** 660.4 mm | 26 in

**Tensile Property Test Method** ASTM D638

**Tensile Strength at yield, minimum** 20.684 N/mm<sup>2</sup> | 3000 psi

**Pulling Tension, maximum** 1,043.262 kg | 2300 lb

## Environmental Specifications

**Environmental Stress Crack Resistance** Failure rate of 10% within 96 hours

**Environmental Stress Test Method** ASTM D1693, ESCR Condition B

## Packaging and Weights

**Weight, net** 702.413 kg/km | 472 lb/kft

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## \* Footnotes

**Environmental Stress Crack Resistance** ESCR—Environmental Stress Crack Resistance