PWRT-210-SN

HELIAX® Remote Radio Head Power Cable, 2 conductor with shield, 10 AWG (5.26 mm2), one Blue Conductor and one Black Conductor

Product Classification

Regional AvailabilityNorth AmericaPortfolioCommScope®Product TypePower cableProduct BrandHELIAX®Product SeriesPWRT

Ordering Note CommScope® non-standard product

General Specifications

Cable TypePowerConductor Type, singlesStranded

Conductors, quantity 2

Construction Type Discrete power cable | Non-armored

Jacket Color Black

Jacket Color, singles Black | Blue

Supported Application Industrial

Dimensions

Diameter Over Conductor, singles, specific0.1260 in per 105 strandsDiameter Over Dielectric4.724 mm | 0.186 inDiameter Over Jacket, nominal11.938 mm | 0.47 inDiameter Over Shield (Braid)9.855 mm | 0.388 inJacket Thickness1.143 mm | 0.045 in


Conductor Gauge, singles 10 AWG

Outer Shield (Braid) Gauge 36 AWG

COMMSCOPE®

PWRT-210-SN

Cross Section Drawing



Electrical Specifications

Conductor dc Resistance 3.478 ohms/km | 1.06 ohms/kft

Conductor dc Resistance Note Maximum value based on a standard condition of 20 °C (68 °F)

Safety Voltage Rating 600 V

Material Specifications

Conductor Material Tinned copper

Dielectric Material PVC

Drain Wire MaterialTinned copperFiller MaterialPolypropyleneGround Wire MaterialTinned copper

Insulation Material, singles PVC

Jacket Material PVC

Outer Shield (Braid) Coverage 85 %

Outer Shield (Braid) Material Tinned copper

Outer Shield (Tape) Material Aluminum/Poly, non-bonded

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +90 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +194 \,^{\circ}\text{F})$

Environmental SpaceUV resistant for outdoor and/or direct burial installations

COMMSCOPE®

PWRT-210-SN

Safety Standard NEC Article 336 (Type TC)

Packaging and Weights

Cable weight 297.633 kg/km | 200 lb/kft

Packaging Type CommPak® box

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

