

# EK2247-000 | TENIO-C6H-NT-0-V



TENIO™ High Density Fiber Optic Splice Closure, Gel Cable sealing, no pre-installed splice trays, with test valve

- Single-ended, toolless closure for splicing feeder, access and drop cables
- Features modular building blocks that fastens installation and reduces inventory
- Gel cable sealing technology allows easy adding or removing of a wide size range of cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- Compatible with CommScope's CWDM modules and optical splitter trays

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Single-ended, rectangular fiber closure
<b>Product Brand</b>	TENIO™
<b>Product Series</b>	TENIO

## General Specifications

<b>Cable Entry Drop Port Style</b>	Gel block
<b>Cable Entry Main Port Style</b>	Gel block
<b>Cable Ports Quantity, total</b>	6 multi-out ports (30 cables)
<b>Cable Sealing Type</b>	Compressed gel
<b>Closure Sealing Type</b>	Side latch
<b>Closure Style</b>	Single-ended
<b>Color</b>	Black
<b>Mounting</b>	Wall
<b>Network Area Type</b>	Distribution   Drop
<b>Splice Tray Included, quantity</b>	0
<b>Splices per Tray, quantity</b>	24
<b>Splicing Capacity, Single Fusion, maximum</b>	288
<b>Splicing Type, Supported</b>	Single fusion

## Dimensions


<b>Height</b>	230 mm   9.055 in
<b>Width</b>	134 mm   5.276 in
<b>Length</b>	449 mm   17.677 in

# EK2247-000 | TENIO-C6H-NT-0-V

**Main Cable Diameter, maximum**

16 mm | 0.63 in

## Ordering Tree



## Material Specifications

**Material Type**

Impact-resistant polymer

## Environmental Specifications

**Environmental Space**

Below ground | Buried

**Qualification Standards**

IEC 61300, 2 m waterhead

**Water Resistance**

Flash test valve at 5 psi (40 kPa)

## Packaging and Weights

**Packaging quantity**

1

**Packaging Type**

Box | Carton

**Weight, net**

1 kg | 2.205 lb

## Regulatory Compliance/Certifications

**Agency**

**Classification**

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

