## EM1621-001 | SCIL-B-48-1-S2-NN



SCIL-B Fiber splice closure, in-line, with 2 gel cable sealing kits, 1 preinstalled 48-splice tray and SMOUV protectors, no ground feedtrough lug , no air valve

- Leverages proven FOSC<sup>™</sup> fiber management system, with multiple splice tray options
- Removeable cover allows unrestricted access to cable termination and splice area for easier installation
- Cable termination and retention system fits any cable type from traditional loose tube buffered to small micro-sheath cables

#### Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Product Type	In-line, rectangular fiber closure
Product Brand	SCIL™
Product Series	SCIL-B
General Specifications	
Cable Entry Drop Port Style	Round
Cable Entry Main Port Style	Round
Cable Ports Quantity, total	4 multi-out ports (24 cables)
Cable Sealing Type	Compressed gel
Closure Sealing Type	Side latch
Closure Style	In-line
Color	Black
Flash Test Valve	None
Ground Feed-through	None
Mounting	Pole   Strand   Wall
Network Area Type	Drop
Splice Tray Included, quantity	1
Splice Tray Type Included	48-way, heat shrink
Splicing Capacity, Single Fusion, maximum	144
Splicing Capacity, Single Splice, 12 fibers, maximum	144
Splicing Type, Supported	Single fusion

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 22, 2024



# EM1621-001 | SCIL-B-48-1-S2-NN

#### Dimensions

Height	106 mm   4.173 in
Width	182 mm   7.165 in
Length	369 mm   14.528 in
Main Cable Diameter, maximum	22 mm   0.866 in

2

٦

4 5

З

## Ordering Tree

зy	type		Cable	e attac	hment	
1	12 Thin tray for 12 fusion splice protectors in single layer, lower style	з		2 cable attachments		
		Thin trau for 12 fusion splice protectors in	-	4	4 cable attachments	
		Grounding				
		4	G	Grounding		
	24	For 24 fusion splice protectors stacked in dual layer, lower style		Ν	No grounding	
	12A	For 12 fusion splices or mechanical splice protectors in single layer, side hinge	Valve 5	V Air valve	Air valve	
	24A	For 24 fusion splice in single layer, side hinge	-	Ν	No valve	
	48	For 48 fusion splice protectors stacked in dual layer, side hinge				
	SMOUV	splice protectors included				
	Numbe	er of trays				
		Up to 4 trays are supported for type 24 trays, 8 trays for type 12 trays, and 3 trays for types 12A, 24A, and 48 trays.				
2 1	Can be ordered with 1 pre-installed trau only.					

## Material Specifications

(see accessories section).

Material Type

#### **Environmental Specifications**

Additional trays must be ordered separately

#### **Environmental Space**

**Qualification Standards** 

### Packaging and Weights

Included

#### Packaging quantity

Rugged polymer

Above ground | Below ground IEC 60529, IP68 + 2 m waterhead

SMOUV splice protectors (48)

1

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 22, 2024

COMMSCOPE®

## EM1621-001 | SCIL-B-48-1-S2-NN

#### Packaging Type

Weight, net

Box | Carton

1 kg | 2.205 lb

### Regulatory Compliance/Certifications

#### Agency


### Classification

CHINA-ROHS

ISO 9001:2015

ROHS

UK-ROHS





Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 22, 2024

