EM1623-001 | SCIL-B-12A-1-S2-NN



SCIL-B Fiber splice closure, in-line, with 2 gel cable sealing kits, 1 preinstalled 12A-splice tray and SMOUV protectors, no ground feedtrough lug, no air valve

- Leverages proven FOSC[™] fiber management system, with multiple splice tray options
- Removeable cover allows unrestricted access to cable termination and splice area for easier installation
- Cable termination and retention system fits any cable type from traditional loose tube buffered to small micro-sheath cables

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America		
Product Type	In-line, rectangular fiber closure		
Product Brand	SCIL™		
Product Series	SCIL-B		
General Specifications			
Cable Entry Drop Port Style	Round		
Cable Entry Main Port Style	Round		
Cable Ports Quantity, total	4 multi-out ports (24 cables)		
Cable Sealing Type	Compressed gel		
Closure Sealing Type	Side latch		
Closure Style	In-line		
Color	Black		
Flash Test Valve	None		
Ground Feed-through	None		
Mounting	Pole Strand Wall		
Network Area Type	Drop		
Splice Tray Included, quantity	1		
Splice Tray Type Included	12-way, heat shrink		
Splicing Capacity, Single Fusion, maximum	96		
Splicing Capacity, Single Splice, 12 fibers, maximum	96		
Splicing Type, Supported	Single fusion		

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 22, 2024



EM1623-001 | SCIL-B-12A-1-S2-NN

Dimensions

Height	106 mm 4.173 in
Width	182 mm 7.165 in
Length	369 mm 14.528 in
Main Cable Diameter, maximum	22 mm 0.866 in

Ordering Tree

		S C I L - B	1	² 1 -	S45			
Tray	j type		Cable	attach	nment			
	12 Thin tray for 12 fusion splice protectors in single layer, lower style	з	2	2 cable attachments				
		This trau for 12 fusion splice protectors in	2	4	4 cable attachments			
		Groun	ding					
		,	G	Grounding				
1		For 24 fusion splice protectors stacked in dual	4		No grounding			
-	24	layer, lower style	Valve					
	12A	For 12 fusion splices or mechanical splice protectors in single layer, side hinge	5			V	Air valve	
	24A	For 24 fusion splice in single layer, side hinge				Ν	No valve	
	48	For 48 fusion splice protectors stacked in dual layer, side hinge						
	SMOUV	splice protectors included						
	Numbe	er of trays						
2	1	Up to 4 trays are supported for type 24 trays, 8 trays for type 12 trays, and 3 trays for types 12A, 24A, and 48 trays.						
C	1	Can be ordered with 1 pre-installed tray only.						

Material Specifications

(see accessories section).

Material Type

Environmental Specifications

Additional trays must be ordered separately

Environmental Space

Qualification Standards

Packaging and Weights

Included

Packaging quantity

Rugged polymer

Above ground | Below ground IEC 60529, IP68 + 2 m waterhead

SMOUV splice protectors (12)

1

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 22, 2024



EM1623-001 | SCIL-B-12A-1-S2-NN

Packaging Type

Weight, net

Box | Carton

1 kg | 2.205 lb

Regulatory Compliance/Certifications

Agency


Classification

CHINA-ROHS

ISO 9001:2015

ROHS

UK-ROHS





Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 22, 2024

