

# NGF-CB1CL2L1082

---



Next Generation Frame (NGF) Fiber Termination/Splice Block, pre-terminated, 96 SC/APC, singlemode, left oriented, putty white

## Product Classification

<b>Regional Availability</b>	EMEA   Latin America   North America
<b>Product Type</b>	Fiber patch/splice block
<b>Product Series</b>	NGF

## General Specifications

<b>Functionality</b>	Patching   Splicing
<b>Application</b>	Used in NGF-style frames only
<b>Body Style</b>	Left orientation
<b>Cable Exit Location</b>	Rear, bottom side
<b>Color</b>	Putty white
<b>Color, front</b>	Putty white
<b>Door Type, front</b>	Compression latch   Hinged
<b>Growth Configuration</b>	Fully loaded
<b>Interface, front</b>	SC/APC
<b>Pigtail Assembly Type</b>	12-fiber, stranded
<b>Pigtails Included, quantity</b>	8
<b>Rack Type</b>	NGF
<b>Shelf Movement</b>	Fixed
<b>Splice Trays Included, quantity</b>	6
<b>Total Ports, quantity</b>	96

## Dimensions

<b>Height</b>	558.8 mm   22 in
<b>Width</b>	166.878 mm   6.57 in

# NGF-CB1CL2L1082

---

**Depth** 495.3 mm | 19.5 in

## Material Specifications

**Finish** Powder coated

**Material Type** Steel

## Optical Specifications

**Fiber Mode** Singlemode

## Environmental Specifications

**Operating Temperature** -5 °C to +50 °C (+23 °F to +122 °F)

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Relative Humidity** Up to 80%, non-condensing

**Qualification Standards** Telcordia GR-449-CORE

## Packaging and Weights

**Included** Mounting hardware

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

