

# NGF-CB4ML2K1126

---



Next Generation Frame (NGF) Fiber Termination/Splice Block, pre-terminated, 144 LC/UPC, singlemode, left oriented, putty white

## Product Classification

<b>Regional Availability</b>	EMEA   Latin America   North America
<b>Product Type</b>	Fiber patch/splice block
<b>Product Series</b>	NGF

## General Specifications

<b>Functionality</b>	Patching   Splicing
<b>Application</b>	Used in NGF-style frames only
<b>Body Style</b>	Left orientation
<b>Cable Exit Location</b>	Rear, bottom side
<b>Color</b>	Putty white
<b>Color, front</b>	Putty white
<b>Door Type, front</b>	Compression latch   Hinged
<b>Growth Configuration</b>	Fully loaded
<b>Interface, front</b>	LC/UPC
<b>Rack Type</b>	NGF
<b>Shelf Movement</b>	Fixed
<b>Splicing Type</b>	Heat shrink, single fiber fusion
<b>Total Ports, quantity</b>	144

## Dimensions

<b>Depth</b>	434.34 mm   17.1 in
--------------	---------------------

## Material Specifications

<b>Finish</b>	Powder coated
---------------	---------------

# NGF-CB4ML2K1126

---

**Material Type** Steel

## Optical Specifications

**Fiber Mode** Singlemode

## Environmental Specifications

**Operating Temperature** -5 °C to +50 °C (+23 °F to +122 °F)

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Relative Humidity** Up to 80%, non-condensing

**Qualification Standards** Telcordia GR-449-CORE

## Packaging and Weights

**Included** Mounting hardware

**Packaging quantity** 1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

