

FDT-AJ012NXF5000



iFDT Indoor Fiber Distribution Terminal, 12-fiber, SC/APC, indoor/outdoor cable, 5000 feet

- Compact and secure family of enclosures by connecting fiber cables at MDUs
- Integrated splice trays offer flexible splice management for individual or mass splicing
- Dual-hinged design ensures separation of owner/client network segments
- Robust steel construction protects fibers against damage and ensures network reliability
- Slotted cable entrance ports allow for rapid cable installation and pass-through capability

Product Classification

Regional Availability	North America
Product Type	Fiber distribution terminal
Product Series	IFDT

General Specifications


Functionality	Patching Splicing
Adapters, quantity	12
Cable Entry Location	Bottom right Top right
Cable Type	Indoor/outdoor - Stranded
Color	Putty white
Front Door Type	Double hinged
Growth Configuration	Fully loaded
Interface	SC/APC
Interface, stub	No connector
Lock Type	Padlock ready
Mounting	Wall
Port, quantity	12

Dimensions

Height	184.15 mm 7.25 in
Width	299.72 mm 11.8 in
Depth	82.55 mm 3.25 in
Cable Length	1524 m 5000 ft

FDT-AJ012NXF5000

Ordering Tree



Material Specifications

- Finish** Powder coated
- Material Type** Steel

Optical Specifications

- Fiber Mode** Singlemode

Environmental Specifications

- Environmental Space** Indoor
- Qualification Standards** NEMA, Type 12 | Telcordia GR-2898-CORE

Packaging and Weights

- Packaging quantity** 1

FDT-AJ012NXF5000

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

