## FDT-AJ012NXV7000



iFDT Indoor Fiber Distribution Terminal, 12-fiber, SC/APC, loose tube IFC cable, 7000 feet

- Compact and secure family of enclosures by connecting fiber cables at MDUs
- Integrated splice trays offer flexible splice management for individual or mass splicing
- Dual-hinged design ensures separation of owner/client network segments
- Robust steel construction protects fibers against damage and ensures network reliability
- Slotted cable entrance ports allow for rapid cable installation and pass-through capability

#### **Product Classification**

Regional Availability North America

**Product Type** Fiber distribution terminal

Product Series IFDT

## General Specifications

Adapters, quantity 12

 Cable Entry Location
 Bottom right | Top right

Cable TypeIFC - StrandedColorPutty whiteFront Door TypeDouble hinged

**Growth Configuration** Fully loaded

Interface SC/APC

Interface, stubNo connectorLock TypePadlock ready

Mounting Wall
Port, quantity 12

#### **Dimensions**

 Height
 184.15 mm | 7.25 in

 Width
 299.72 mm | 11.8 in

 Depth
 82.55 mm | 3.25 in


 Cable Length
 2,133.6 m | 7000 ft

### Ordering Tree



Page 1 of 3

# FDT-AJ012NXV7000



### Material Specifications

**Finish** Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

#### **Environmental Specifications**

Environmental Space Indoor

**Qualification Standards** NEMA, Type 12 | Telcordia GR-2898-CORE

Packaging and Weights

Packaging quantity 1



# FDT-AJ012NXV7000

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

