

760210740 | HD-2U-FX



High Density 2U modular cassette fixed Panel, accepts (8) G2 modules or MPO panels, providing up to 96 duplex LC ports or up to 64 MPO ports

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	HD

General Specifications

Application	Accepts eight G2 modular cassettes
Color	Black + Silver gray (front)
Intelligence Type	iPatch® ready
Interface, front	Unloaded
Rack Type	EIA 19 in
Rack Units	2
Shelf Movement	Fixed
Total Ports, quantity	0

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in
Depth	467.11 mm 18.39 in

Material Specifications

Material Type	Steel
---------------	-------

Environmental Specifications

Flammability Rating	UL 94 V-0
Safety Standard	UL 1863

Packaging and Weights

Packaging quantity	1
Weight, net	5.262 kg 11.6 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

