## RCP-47APU009200



RapidFiber® Termination Panel, 144-Position 4RU, singlemode, SC/UPC to stub, 92 m

#### **Product Classification**

Regional Availability Latin America | North America

Portfolio CommScope®

**Product Type** Fiber patch panel, with rapid cable

Product Brand RapidFiber®

Product Series RCP

### General Specifications

**Functionality** Patching

Body Style Symmetrical

Cable Exit Location Rear, left side

Cable Stub Type Indoor, microcable

**Color** Putty white

Door Type, front Hinged | Slide latch | Transparant

Growth ConfigurationFully loadedInterface, frontSC/UPCInterface, rearStub tail

Patch Cord Entry Location Front, left side | Front, right side

Rack Type EIA 19 in | EIA 23 in

Rack Units 4

Shelf MovementSlidingTotal Fibers, quantity144Total Ports, quantity144

**Transmission Standards** IEC 60794-2 | ISO/IEC 11801 | TIA/EIA-568-B.3

**Dimensions** 

**Height** 177.8 mm | 7 in

COMMSCOPE®


# RCP-47APU009200

 Width
 482.6 mm | 19 in

 Depth
 381 mm | 15 in

 Cable Length
 92 m | 301.837 ft

## Ordering Tree



## Material Specifications

**Finish** Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

**Fiber Type** G.652.D | G.657.A2/B2

COMMSC PE®

# RCP-47APU009200

## **Environmental Specifications**

Operating Temperature  $-5 \,^{\circ}\text{C}$  to  $+55 \,^{\circ}\text{C}$  (+23  $^{\circ}\text{F}$  to +131  $^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to +158  $^{\circ}\text{F}$ )

**Relative Humidity** 5%–85%, non-condensing

Qualification Standards NEBS Level 3 | Telcordia GR-1435 | Telcordia GR-326 | Telcordia GR-409 | UL 1863

## Packaging and Weights

Packaging quantity 1

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

