RCP-47APUE06100



RapidFiber® Termination Panel, 144-Position 4RU, singlemode, SC/UPC to MPO, 61 m

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel, with rapid cable

Product Brand RapidFiber®

Product Series RCP

General Specifications

Functionality Patching

Body Style Symmetrical **Cable Exit Location** Rear, left side

Cable Stub Type Indoor, microcable

Color Putty white

Door Type, front Hinged | Slide latch | Transparant

Growth Configuration Fully loaded Interface, front SC/UPC MPO

Interface, rear

Patch Cord Entry Location Front, left side | Front, right side

EIA 19 in | EIA 23 in **Rack Type**

Rack Units 4

Shelf Movement Sliding **Total Fibers, quantity** 144 **Total Ports, quantity** 144

Transmission Standards IEC 60794-2 | ISO/IEC 11801 | TIA/EIA-568-B.3

Dimensions

Height 177.8 mm | 7 in

COMMSCOPE®


RCP-47APUE06100

 Width
 482.6 mm | 19 in

 Depth
 381 mm | 15 in

 Cable Length
 61 m | 200.131 ft

Ordering Tree



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.652.D | G.657.A2/B2

COMMSC PE°

RCP-47APUE06100

Environmental Specifications

Operating Temperature $-5 \,^{\circ}\text{C} \text{ to } +55 \,^{\circ}\text{C} \text{ (+23 °F to +131 °F)}$

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity 5%–85%, non-condensing

Qualification Standards NEBS Level 3 | Telcordia GR-1435 | Telcordia GR-326 | Telcordia GR-409 | UL 1863

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

