# 760240481 | FACT-2ELHPSFA



FACT® Fiber Optic Patch/Splice Chassis, gray, 2E high, 48-port, singlemode, loaded with SC/UPC adapters and B-grade pigtails, ANT splice tray type, left-hand patch

- Designed for use with the all-purpose all-front-access FACT frames and FIST-GR3 frames supporting up to 2,688 LC or 1,344 SC connections in a single frame (FACT-IC frame 2880 LC or 1440 SC)
- Reduced installation and maintenance time via the toolless snap-on design supporting both interconnect and cross-connect applications
- Flexible customization enabled by 4 chassis types (patch-only, patch-splice, pre-cabled and splice-only) to support all ODF applications
- High density through the single FACT element height (1E) being 30% less tall compared to the industry standard panel height (1HU)

### Product Classification

| Regional Availability  | Asia   Australia/New Zealand   EMEA   Latin America   North America |
|------------------------|---|
| Portfolio              | CommScope®  |
| Product Type           | Fiber patch/splice chassis  |
| Product Brand          | FACT®   |
| Product Series         | FACT  |
| General Specifications |   |
| Functionality          | Patching   Splicing   |
|                        |   |

| ,                           | · · · · · · · · · · · · · · · · · · · |
|-----------------------------|---------------------------------------|
| Application                 | Compatible with FIST-GR3-style frames |
| Body Style                  | Left-hand patch                       |
| Color                       | Gray                                  |
| Growth Configuration        | Fully loaded                          |
| Interface, front            | SC/UPC                                |
| Patch Cord Routing          | Left sided                            |
| Pigtail Assembly Type       | 12-fiber, stranded                    |
| Pigtails Included, quantity | 48                                    |
| Rack Type                   | EIA 19 in                             |
| Rack Units                  | 1.4                                   |
| Shelf Movement              | Sliding                               |
| Splicing Capacity, maximum  | 48                                    |
|                             |                                       |

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 21, 2024




# 760240481 | FACT-2ELHPSFA

| Splicing Type          | ANT                                  |
|------------------------|--------------------------------------|
| Total Ports, quantity  | 48                                   |
| Transmission Standards | ETSI EN 300 019-1-3   IEC 61300-3-30 |
| Dimensions             |                                      |
| Height                 | 61.9 mm   2.437 in                   |
| Width                  | 524 mm   20.63 in                    |

## Ordering Tree

Depth



283 mm | 11.142 in

### Optical Specifications

| Fiber Mode              | Singlemode       |
|-------------------------|------------------|
| Fiber Type              | G.657.A1         |
| Performance Grade       | Superior B grade |
| Insertion Loss, maximum | 0.5 dB           |
| Return Loss, minimum    | 50 dB            |

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 21, 2024

element



# 760240481 | FACT-2ELHPSFA

#### **Environmental Specifications**

| Operating Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
|-----------------------|--------------------------------------|
| Storage Temperature   | -20 °C to +85 °C (-4 °F to +176 °F)  |
| Flammability Rating   | UL 94 V-0                            |

#### Packaging and Weights

| Included           | Mounting hardware for FACT frame |
|--------------------|----------------------------------|
| Packaging quantity | 1                                |

#### Regulatory Compliance/Certifications

| CHINA-ROHS    | Above maximum concentration value  |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant/Exempted   |
|               |  |



### \* Footnotes

Performance Grade Guarantee to meet IEC 61755-1 Random Mating requirement

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 21, 2024

