CJ9789-000 | FIST-GC02-FC6-NN



FIST® GCO2 Fiber Optic Splice Closure, Heat Shrink or Gold Gel Cable sealing, size FC, no pre-installed fiber trays, 6 round ports + 1 oval port

- Single-ended, O-ring sealed dome closure for splicing feeder and distribution cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- Universal mounting system (UMS) profiles provide foundation for mounting combinations of FIST splice trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

Product Classification

Regional Availability EMEA

Product Type Single-ended, rectangular fiber closure

Product Brand FIST®

Product Series FIST-GC02

General Specifications

Cable Entry Drop Port StyleRoundCable Entry Main Port StyleOval

Cable Ports Quantity, total1 oval port (2 cables) + 6 round ports

Cable Sealing Type Gel kit (optional) | Heat shrink

Closure Sealing Type Base and dome sealed with latches and O-ring system

Closure Style Single-ended

ColorBlackFlash Test ValveNoneGround Feed-throughNone

Mounting Pole | Strand | Wall

Network Area Type Distribution

Splice Tray Included, quantity 0

Splice Tray Type IncludedNo traysSplicing Capacity, Mass Fusion, maximum288Splicing Capacity, Single Fusion, maximum384

Splicing Type, Supported Mass fusion | Single fusion



CJ9789-000 | FIST-GC02-FC6-NN

Dimensions

 Height
 279 mm | 10.984 in


 Width
 150 mm | 5.906 in

 Length
 384 mm | 15.118 in

 Cable Entry Drop Port Diameter
 30 mm (1.18 in) mm

 Main Cable Diameter, maximum
 25 mm | 0.984 in

Dimension Drawing




Splicing Configuration

	FC		FD	
UMS Units	16		24	
# SC/SLE 4mm trays		16		24
# SE 8mm trays		8	ja .	12
# SHD 4mm trays		16		24
# R12 12mm FLAT ribbon trays		5		8
Max. Single splice capacity SC trays (4F/SC)		64		96
Max. Single splice capacity high dense trays (12F/SLE)		192		288
Max. Single splice capacity SE trays (12F/SE)		96	6	144
Max. Single splice capacity Super high dense trays (24F/SHD)		384		576
Max. mass splice capacity R12 trays (FLAT ribbon)		120	11	192
Max. mass splice capacity SE trays (Rollable ribbon G657A2 fiber)		288		432

Ordering Tree



CJ9789-000 | FIST-GC02-FC6-NN



Material Specifications

Material Type Impact-resistant polymer

Environmental Specifications

Environmental SpaceBelow ground | BuriedQualification StandardsIEC 61300, 5 m waterhead

Packaging and Weights

Packaging quantity 1

Packaging TypeBox | CartonWeight, net3.3 kg | 7.275 lb

Regulatory Compliance/Certifications

Agency Classification CHINA-ROHS Below maximum concentration value ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance ROHS Compliant UK-ROHS Compliant

