

CU2623-000 | OWB-S-NO-S21-NN-W



OWB Fiber Optic Wall Mount Fiber Box, 1 SC/APC adapter, no splicing, no splitters

- Compact sized with multiple cable entry point options
- Used as a premises connection device in FTTH networks
- Easy access via the combined hinge + latch design
- High sealing rate, UV resistant and UL compliant
- Slack storage (3 mtr) for drop- and premise connection cable

Product Classification

Regional Availability	Asia Australia/New Zealand Latin America North America
Product Type	Fiber wall box
Product Series	OWB

General Specifications


Functionality	Patching
Access	Front
Application	For cables with outer diameter 3 x 5.4 mm: 1 on top + 1 on bottom For cables with outer diameter up to 10 mm: each on both sides For cables with outer diameter up to 5 mm: 1 on rear + 4 on bottom
Enclosure Color	Gray
Front Cover Type	Hinged with latches
Interface	SC/APC
Lock Type	Ski latch and screw
Mounting	Wall
Port Capacity, maximum	4
Port, quantity	1

Dimensions

Height	209.8 mm 8.26 in
Width	173.74 mm 6.84 in
Depth	71.88 mm 2.83 in

Dimension Drawing

CU2623-000 | OWB-S-NO-S21-NN-W



Material Specifications

Enclosure Material Type LSZH thermoplastic

Optical Specifications

Fiber Mode Singlemode

Insertion Loss, Terminal Connector, maximum 0.3 dB

Environmental Specifications

Installation temperature -5 °C to +45 °C (+23 °F to +113 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Environmental Space Outdoor

Flammability Rating UL 94 V-0

Qualification Standards IEC 60529, IP65

Packaging and Weights

Included Grommets

Packaging quantity 1

Packaging Type Box | Carton

Regulatory Compliance/Certifications

CU2623-000 | OWB-S-NO-S21-NN-W

Agency

CHINA-ROHS
REACH-SVHC
ROHS
UK-ROHS

Classification

Below maximum concentration value
Compliant as per SVHC revision on www.commscope.com/ProductCompliance
Compliant
Compliant

