

CV6800-000 | TENIO-B6-S12-12-V



TENIO™ Small Fiber Optic Splice Closure, Gel Cable sealing, 12 pre-installed 12-fiber trays, 12 heat shrink splice protectors (SMOUV 45 mm), with test valve

- Single-ended, toolless closure for splicing feeder, access and drop cables
- Features modular building blocks that fastens installation and reduces inventory
- Gel cable sealing technology allows easy adding or removing of a wide size range of cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- Compatible with CommScope's CWDM modules and optical splitter trays

Product Classification

Regional Availability	EMEA Latin America
Product Type	Single-ended, rectangular fiber closure
Product Brand	TENIO™
Product Series	TENIO

General Specifications

Cable Entry Drop Port Style	Gel block
Cable Entry Main Port Style	Gel block
Cable Ports Quantity, total	6 multi-out ports (30 cables)
Cable Sealing Type	Compressed gel
Closure Sealing Type	Side latch
Closure Style	Single-ended
Color	Black
Mounting	Wall
Network Area Type	Distribution Drop
Splice Tray Included, quantity	12
Splice Tray Type Included	12-way, heat shrink
Splices per Tray, quantity	12
Splicing Capacity, Single Fusion, maximum	144
Splicing Type, Supported	Single fusion


Dimensions

Height	230 mm 9.055 in
---------------	-------------------

CV6800-000 | TENIO-B6-S12-12-V

Width	134 mm 5.276 in
Length	389 mm 15.315 in
Main Cable Diameter, maximum	16 mm 0.63 in

Ordering Tree



Material Specifications

Material Type Impact-resistant polymer

Environmental Specifications

Environmental Space Below ground | Buried

Qualification Standards IEC 61300, 2 m waterhead

Water Resistance Flash test valve at 5 psi (40 kPa)

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

Weight, net 1 kg | 2.205 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

CV6800-000 | TENIO-B6-S12-12-V

ROHS

Compliant

