D83168-000 | F0SC400-A8-12-1-NGV



FOSC® 400 A8 Fiber Optic Splice Closure, Heat Shrink Cable sealing, one pre-installed 12-splice tray, with test valve

- Single-ended, O-ring sealed dome closure for splicing feeder and distribution cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- FOSC splice trays hinged for access to any splice without disturbing other trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

Product Classification

 Regional Availability
 Latin America | North America

 Product Type
 Single-ended, round fiber closure

Product Brand FOSC®
Product Series FOSC 400

General Specifications

 Cable Blocking Components
 None

 Cable Entry Drop Port Style
 Round

 Cable Entry Main Port Style
 Oval

Cable Ports Quantity, total 1 oval port (2 cables) + 8 round ports

Cable Sealing Type Heat shrink

Closure Sealing Type Dome-to-base clamp with 0-ring

Closure Style Single-ended

Color Black

Flash Test Valve Pre-installed
Ground Feed-through Included

Mounting Pole | Strand | Wall

Network Area Type Feeder

Splice Tray Included, quantity

Splice Tray Type Included 12-way, heat shrink

Splicing Capacity, Mass Fusion, maximum 144
Splicing Capacity, Single Fusion, maximum 96
Splicing Capacity, Single Splice, 12 fibers, maximum 96

COMMSC PE®

D83168-000 | F0SC400-A8-12-1-NGV

Splicing Capacity, Single Splice, 6 fibers, maximum

Splicing Type, Supported Single fusion

Dimensions


 Length
 420 mm | 16.535 in

 Diameter
 150 mm | 5.906 in

 Diameter, with clamp
 180 mm | 7.087 in


 Main Cable Diameter, maximum
 25 mm | 0.984 in

Dimension Drawing




Base Ports Configuration

48



Ordering Tree

D83168-000 | F0SC400-A8-12-1-NGV



*Note: SMOUV (1120-01-US) splice protection sleeves should be used with SM12 splice modules.

Material Specifications

Material Type Impact-resistant polymer

Environmental Specifications

Environmental Space Below ground | Buried

Qualification Standards IEC 61300, 6 m waterhead

Water Resistance Flash test valve at 5 psi (40 kPa)

Packaging and Weights

Packaging quantity

Packaging TypeBox | CartonWeight, net2.4 kg | 5.291 lb

Weight, net 2.4

Agency	Classification

CHINA-ROHS Below maximum concentration value

Regulatory Compliance/Certifications

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

COMMSCOPE®

D83168-000 | FOSC400-A8-12-1-NGV

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

