# 760240648 | FACT-4ERHPLFS



FACT® Fiber Optic Patch/Splice Chassis, gray, 4E high, 192-port, singlemode, loaded with LC/UPC adapters and B-grade pigtails, SMOUV splice tray type, right-hand patch

- Designed for use with the all-purpose all-front-access FACT frames and FIST-GR3 frames supporting up to 2,688 LC or 1,344 SC connections in a single frame (FACT-IC frame 2880 LC or 1440 SC)
- Reduced installation and maintenance time via the toolless snap-on design supporting both interconnect and cross-connect applications
- Flexible customization enabled by 4 chassis types (patch-only, patch-splice, pre-cabled and splice-only) to support all ODF applications
- High density through the single FACT element height (1E) being 30% less tall compared to the industry standard panel height (1HU)

## Product Classification

**Pigtails Included, quantity** 

Splicing Capacity, maximum

**Rack Type** 

**Rack Units** 

Shelf Movement

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America	
Portfolio	CommScope®	
Product Type	Fiber patch/splice chassis	
Product Brand	FACT®	
Product Series	FACT	
General Specifications		
Functionality	Patching   Splicing	
Application	Compatible with FIST-GR3-style frames	
Body Style	Right-hand patch	
Color	Gray	
Growth Configuration	Fully loaded	
Interface, front	LC/UPC	
Patch Cord Routing	Right sided	
Pigtail Assembly Type	12-fiber, stranded	

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 21, 2024

192

2.8

192

Sliding

EIA 19 in




## 760240648 | FACT-4ERHPLFS

Splicing Type	SMOUV
Total Ports, quantity	192
Transmission Standards	ETSI EN 300 019-1-3   IEC 61300-3-30
Dimensions	
Height	123.8 mm   4.874 in
Width	524 mm   20.63 in

## Ordering Tree

Depth



283 mm | 11.142 in

## Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A1
Performance Grade	Superior B grade
Insertion Loss, maximum	0.5 dB
Return Loss, minimum	50 dB

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 21, 2024

element



## 760240648 | FACT-4ERHPLFS

### **Environmental Specifications**

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-20 °C to +85 °C (-4 °F to +176 °F)
Flammability Rating	UL 94 V-0

### Packaging and Weights

Included	Mounting hardware for FACT frame
Packaging quantity	1

## Regulatory Compliance/Certifications

Agency
--------

#### Classification

CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



### \* Footnotes

Performance Grade Guarantee to meet IEC 61755-1 Random Mating requirement

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 21, 2024

