

FDH 3000 Plug-and-Play Splitter Module, 1 x 32, SC/APC

- Rugged packaging is built for high performance, while the Plug-and-Play design reduces installation time
- Bend-optimized fiber and ruggedized extreme temperature cabling
- Easy to insert and remove without affecting adjacent splitters
- Reversible dust cap makes test and turn-up easy
- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Splitter module
Product Series	FDH 3000 Mini FDH 3000
Government Requirements	Build America Buy America (BABA) compliant*
General Specifications	
Device Type	Plug-and-play module
Functionality	Splitting
Access	Front Rear
Application	For use in FDH 3000 cabinets
Circuits, quantity	1
Distribution Type	1 x 32 splitter
Interface, front	SC/APC
Interface, Input	SC/APC
Interface, Output	SC/APC
Interface, rear	SC/APC
Location of Manufacturing	Waived per BABA waiver for BEAD Program
Module Color	Putty white
Split Ratio	Symmetrical
Splitter, quantity	1

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 4, 2024

COMMSCOPE°

FPS-LPP1AJJ

Dimensions

Height	88.9 mm 3.5 in
Width	12.7 mm 0.5 in
Depth	139.7 mm 5.5 in
Furcation Tube Diameter	2 mm 0.079 in

Optical Specifications

Directivity, minimum	55 dB
Polarization Dependent Loss, maximum	0.3 dB
Uniformity, maximum	1.6 dB
Wavelength Range	1260-1650 nm
Insertion Loss, Splitter, maximum	17 dB
Return Loss, Splitter, minimum	55 dB

Environmental Specifications

Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Flammability Rating	UL 94 V-0
Qualification Standards	Telcordia GR-1209-CORE Telcordia GR-1221-CORE Telcordia GR-326-CORE
Packaging and Weights	
Included	Reversible dust cap

Packaging quantity	1		
Packaging Type	Bag	I	Carton

Regulatory Compliance/Certifications

Classification
Below maximum concentration value
Compliant as per SVHC revision on www.commscope.com/ProductCompliance
Compliant
Compliant



Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 4, 2024

