


760241517 | EPX-1U-MOD-OPEN-F-FX (AGL-1U-FX)



EPX 1U fixed panel, accepts (4) G2 modules or adapter packs providing up to 48 duplex LC or 32 MPO ports

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	EPX

General Specifications

Application	Accepts four G2 modular cassettes
Color	Black
Intelligence Type	Not iPatch® ready
Interface, front	Unloaded
Rack Type	EIA 19 in
Rack Units	1
Shelf Movement	Fixed
Total Ports, quantity	0

Dimensions

Height	44 mm 1.732 in
Width	482.6 mm 19 in
Depth	232 mm 9.134 in

Material Specifications

Finish	Powder coated
Material Type	Steel

Environmental Specifications

Safety Standard	UL
------------------------	----

Packaging and Weights

Packaging quantity 1
Weight, net 0.907 kg | 2 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

