



G2 Modular Cassette with 6 ST TeraSPEED® Singlemode Pigtails, Type A

OBSOLETE

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Fiber cassette with pigtails
Product Brand	TeraSPEED®

General Specifications

Adapter Color	Blue
Interface, front	ST/UPC
Interface, rear	Stranded pigtail
Total Fibers, quantity	6
Total Ports, quantity, front	6

Dimensions

Height	30.48 mm 1.2 in
Width	91.44 mm 3.6 in
Depth	119.38 mm 4.7 in
Pigtail Length	1.5 m 4.921 ft

Optical Specifications

Fiber Type	G.652.D and G.657.A1, TeraSPEED® OS2
Insertion Loss, typical	0.4 dB
Return Loss, minimum	55 dB

Environmental Specifications

760032276 | MODG2-6ST-SM-PT-A

Safety Standard UL

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Included Products

760049767	–	TeraSPEED® ST Multiport Shuttered Adapter, Blue, Single Pack
SFA-ST06-BL-SHUTTERED		

760049767 | SFA-ST06-BL-SHUTTERED



TeraSPEED® ST Multiport Shuttered Adapter, Blue, Single Pack

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber adapter
Product Brand	TeraSPEED®
Product Series	SFA

General Specifications

Body Style	Ganged
Color	Blue
Interface	ST/UPC
Mounting	No flange
Shuttered	Yes
Total Ports, quantity	6

Material Specifications

Alignment Sleeve Material	Zirconia
---------------------------	----------

Optical Specifications

Fiber Mode	Singlemode
------------	------------

Packaging and Weights

Packaging quantity	1
--------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

