

MFPS Fiber Optic panel, 3RU, 48 fibers/RU, splice/patch, SMOUV/front patch cords orientation to the right, 144 SC/APC, Grade C

- Suitable for cabinets and POP locations
- Various available panel heights to support termination counts from 12 to 288
- Simple wrap-around design for easy fiber routing
- Supports patch cord diameters of 1.2 to 2.4mm (XD-series require the usage of 1.2mm patch cords)

### Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	MFPS

### General Specifications

Functionality	Patching   Splicing
Cable Exit Location	Rear   Side
Color	Gray
Door Type, front	Compression latch   Hinged
Growth Configuration	Fully loaded
Interface, front	SC/APC
Patch Cord Entry Location	Front, right side
Patch Cord Routing	Right sided
Pigtail Assembly Type	Color-coded, 900 µm
Pigtails Included, quantity	144
Rack Type	EIA 19 in   ETSI 600 mm
Rack Units	3
Shelf Movement	Hinged
Splicing Type	Heat shrink, single fiber fusion
Total Ports, quantity	144
Transmission Standards	ETSI EN 300 019-1-3   IEC 61300-3-34

### Dimensions


EK3431-000 | MFPS-IHD-P-SIS2-144

<b>Height</b>	125 mm   4.921 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	279.91 mm   11.02 in

## Port Configuration

MFPS Capacities		48		72	96
Connector Type		SC	LC	LC	LC Adapter Pack
19 inch	1HU	48	48	72	96
	2HU	96	96	144	192
	2.8 HU	144	144	216	288

## Ordering Tree



## Material Specifications

Finish	Powder coated
Material Type	Ethylene-propylene (EP)   Polyethylene terephthalate (PET)

## Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A1
Performance Grade	Standard C grade

## Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-20 °C to +85 °C (-4 °F to +176 °F)
Flammability Rating	UL 94 V-0

## Packaging and Weights

Included	Mounting hardware   Two cable termination kits
Packaging quantity	1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

Performance Grade	Guarantee to meet IEC 61755-1 Random Mating requirement
-------------------	---