

# FEC-10K



## Fiber Optic Entrance Cabinet, up to 10,368 ribbon fibers

- Provides splicing, administration and storage for outside plant (OSP) and intrafacility cables (IFC)
- Offers a cost-effective, space-saving alternative to splicing on the fiber frame
- Cabinets are designed for deployment in a building equipment area
- Bend radius protection and discrete subunit routing paths ensure easy installation
- Can deploy high count of stranded or ribbon fiber cables

### **OBSOLETE**

This product was discontinued on: **October 31, 2019**

#### Replaced By:

FEC-36

Fiber Optic Entrance Cabinet, 36 Drawers, Wall mounted

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand   Latin America   North America
<b>Product Type</b>	Fiber entrance cabinet
<b>Product Series</b>	FEC

## General Specifications

<b>Access</b>	Front
<b>Cable Entry Location</b>	Bottom   Top
<b>Cable Exit Location</b>	Side
<b>Color</b>	Putty white
<b>Mounting</b>	Wall
<b>Splice Drawers, quantity</b>	36
<b>Splice Trays Included, quantity</b>	0
<b>Splicing Capacity Note</b>	up to 10368 ribbon fibers
<b>Splicing Capacity, maximum</b>	10368

## Dimensions

<b>Height</b>	1575 mm   62.008 in
<b>Width</b>	813 mm   32.008 in
<b>Depth</b>	330 mm   12.992 in

# FEC-10K

---

## Environmental Specifications

**Environmental Space** Indoor

## Packaging and Weights

**Included** Grommets

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

