

FEC-18-RM



Fiber Optic Entrance Cabinet, 18 Drawers, Rack mounted

- Provides splicing, administration and storage for outside plant (OSP) and intrafacility cables (IFC)
- Offers a cost-effective, space-saving alternative to splicing on the fiber frame
- Cabinets are designed for deployment in a building equipment area
- Bend radius protection and discrete subunit routing paths ensure easy installation
- Can deploy high count of stranded or ribbon fiber cables
- Ultra high density splice capacity dependent on splice tray used

Product Classification

Regional Availability	Australia/New Zealand Latin America North America
Product Type	Fiber entrance cabinet
Product Series	FEC

General Specifications

Access	Front Rear
Cable Entry Location	Bottom Side Top
Cable Exit Location	Bottom Side Top
Color	Putty white
Mounting	Rack, EIA 23 in
Splice Drawers, quantity	18
Splice Trays Included, quantity	0
Splicing Capacity Note	18 times number of splices per tray (example 18x288 = 5184)

Dimensions

Height	914.4 mm 36 in
Width	660.4 mm 26 in
Depth	381 mm 15 in

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

Packaging and Weights

Included	Grommets
-----------------	----------

FEC-18-RM

Regulatory Compliance/Certifications

Agency**Classification**

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

