# H96547-000 | FOSC450-D6-6-72-4-NOV



#### FOSC® 450 D6 Fiber Optic Splice Closure, Gel Cable sealing, four preinstalled 72-splice trays, 6 cable attachments, with test valve

- Single-ended, O-ring sealed dome closure for splicing feeder and distribution cables
- Gel cable sealing technology allows easy adding or removing of a wide size range of cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- FOSC splice trays hinged for access to any splice without disturbing other trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

#### Product Classification

Regional Availability	Latin America   North America
Product Type	Single-ended, round fiber closure
Product Brand	FOSC®
Product Series	FOSC 450
General Specifications	
Cable Entry Drop Port Style	Round
Cable Entry Main Port Style	Round
Cable Ports Quantity, total	6 round ports
Cable Sealing Type	Compressed gel
Closure Sealing Type	Dome-to-base clamp with O-ring
Closure Style	Single-ended
Color	Black
Fiber Storage Basket Type	No basket
Flash Test Valve	Pre-installed
Ground Feed-through	None
Mounting	Pole   Strand   Wall
Network Area Type	Feeder
Splice Tray Included, quantity	4
Splice Tray Type Included	72-way, heat shrink
Splicing Capacity, Mass Fusion, maximum	3456
Splicing Capacity, maximum	3456

Page 1 of 4


©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 6, 2024



# H96547-000 | FOSC450-D6-6-72-4-NOV

Splicing Capacity, Single Fusion, maximum	768
Splicing Capacity, Single Splice, 12 fibers, maximum	576
Splicing Capacity, Single Splice, 6 fibers, maximum	288
Splicing Type, Supported	Mass fusion   Single fusion
Dimensions	
Length	753 mm   29.646 in
Diameter	254 mm   10 in
Diameter, with clamp	292 mm   11.496 in
Main Cable Diameter, maximum	25 mm   0.984 in

### Dimension Drawing




## Ordering Tree

Page 2 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 6, 2024

**COMMSCOPE**°



### Material Specifications

**Material Type** 

**Environmental Space** 

**Qualification Standards** 

Water Resistance

#### Packaging and Weights

Packaging quantity	1
Packaging Type	Box   Carton
Weight, net	9.07 kg   19.996 lb

Impact-resistant polymer

Below ground | Buried

IEC 61300, 5 m waterhead

Flash test valve at 5 psi (40 kPa)

Page 3 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 6, 2024

COMMSCOPE®

# H96547-000 | FOSC450-D6-6-72-4-NOV

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum
ISO 9001:2015	Designed, manufa
REACH-SVHC	Compliant as per

Below maximum concentration value Designed, manufactured and/or distributed under this quality management system Compliant as per SVHC revision on www.commscope.com/ProductCompliance Compliant



**UK-ROHS** 

ROHS



©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 6, 2024

