RCP-172PU703139



RapidFiber® Termination Panel, 24-Position 1RU, singlemode, dual 12-fiber 3 mm plenum-rated, 31 m, 39 in breakout

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel, with rapid cable

Product Brand RapidFiber®

Product Series RCP

General Specifications

Functionality Patching

Body Style Symmetrical

Cable Exit LocationRear, left side

Cable Stub TypeIndoor, microcable

Color Putty white

Door Type, front Hinged | Slide latch | Transparant

Growth ConfigurationFully loadedInterface, frontSC/UPCInterface, rearSC/UPC

Patch Cord Entry Location Front, left side | Front, right side

Rack Type EIA 19 in | EIA 23 in

Rack Units 1

Shelf Movement Sliding

Total Fibers, quantity 24

Total Ports, quantity 24

Transmission Standards IEC 60794-2 | ISO/IEC 11801 | TIA/EIA-568-B.3

Dimensions

 Height
 44.45 mm | 1.75 in

 Width
 482.6 mm | 19 in


COMMSCOPE®

RCP-172PU703139

Depth 381 mm | 15 in

Cable Length 31 m | 101.706 ft

Ordering Tree



ONLY FOR MULTIMODE VERSION. 1
ONLY AVAILABLE IN RISER/PLENUM (P) CABLE TYPE²
RAPID PANEL IS DESIGNED AND QUALIFIED FOR UP TO 1000' (305 METERS) OF CABLE. 3
ONLY AVAILABLE IN 1C288 4912

Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.652.D | G.657.A2/B2

COMMSCOPE®

RCP-172PU703139

Environmental Specifications

Operating Temperature $-5 \,^{\circ}\text{C}$ to $+55 \,^{\circ}\text{C}$ (+23 $^{\circ}\text{F}$ to +131 $^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)

Relative Humidity 5%–85%, non-condensing

Qualification Standards NEBS Level 3 | Telcordia GR-1435 | Telcordia GR-326 | Telcordia GR-409 | UL 1863

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

