

MST, Fiber Optic Multiport Service Terminal, 12-port, long 2xN port, locatable flat loose tube cable, 2000 ft

- Hardened connectors are factory-terminated and environmentally sealed for use in optical drop cable deployments
- Plug and play adapter ports ensure rapid cable installment in the outside plant access section of the network
- Multiport Service Terminals incorporate hardened connector technology that is designed to withstand the rugged outside plant environment

Alternative products available:

HST-BCHNB2000NN000 HST, NOVUX™ Hardened Standard Terminal, 12-port, Flat toneable loose tube cable, 2000 ft/609 m

Product Classification

Regional Availability

Asia | Latin America | North America

Product Type Access terminal, without splitter/tap

Product Series MST

General Specifications

Cable Type Locatable - Flat - Loose Tube

Cable, quantity

Distribution Type12 portsEnclosure ColorBlack

Mounting Handhole | Pedestal | Pole | Strand

Port Type Hardened full-size SC/APC

Port, quantity 12
Splitter, quantity 0

Stub Type Stub tail

Dimensions

 Height
 546.9 mm | 21.532 in

 Width
 129.5 mm | 5.098 in

 Depth
 84.1 mm | 3.311 in

COMMSCOPE®


Cable Length, stub


2000 ft (609 m)

Cable Outer Diameter


5.0 mm (0.20 in)

Dimension Drawing





Ordering Tree



Material Specifications

Enclosure Material Type

Gasketed hardened plastic

COMMSCOPE®

Optical Specifications

Fiber Type G.657.A1/A2

Operating Wavelength Range 1260 – 1635 nm

Attenuation Cable Coefficient, maximum 0.30 dB/km @ 1550 nm | 0.40 dB/km @ 1310 nm

Attenuation Terminal Connectors, maximum0.4 dBDirectivity, minimum60 dBInsertion Loss, Terminal Connector, typical0.16 dB

Return Loss, Connector, minimum 65 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Relative Humidity 5%-100%, condensing

Environmental Space Above ground | Below ground | Buried

Flammability Rating UL 94 5VA

Qualification Standards IEC 60529, IP68 + 2 m waterhead | Telcordia GR-3120-CORE | Telcordia

GR-326-CORE | Telcordia GR-771-CORE

UV Resistance UV stabilized

Packaging and Weights

Included Enclosure (1) | Universal mounting bracket (1)

Packaging quantity 1

Packaging TypeBox | CartonWeight, without cable2.31 kg | 5.093 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





Included Products

MST-UMB-0012

DLX® MST, Fiber Optic Universal Mounting Bracket, 12 port



DLX® MST, Fiber Optic Universal Mounting Bracket, 12 port

Product Classification

Regional Availability EMEA | Latin America | North America

Product Type Mounting bracket

Product Series MST

General Specifications

Color Black

Environmental Specifications

Environmental Space Outdoor

Packaging and Weights

Packaging quantity

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



COMMSCOPE®