

# NDX-06BTMOU-A1500F



## DLX® Fiber Indexing Terminal, 1x4 Splitter, 4 Forward Ports, 1 Reverse Port, Dielectric Flat Loose Tube Cable, 1500 Feet

- Fiber Indexing terminals are access terminals using hardened connectivity technology that withstand the rugged outside plant environment
- Fiber Indexing terminals eliminate splicing and use 12-strand fiber cable in a daisy-chain topology, reducing the total required cable length by up to 70%
- Hardened adapters are factory-terminated and environmentally sealed to ensure rapid plug-and-play drop cable installations

### Product Classification

Regional Availability	North America
Product Type	Access terminal, indexed with splitter
Product Brand	DLX®
Product Series	NDX

### General Specifications

Cable Type	Dielectric - Flat - Loose Tube
Cable, quantity	1
Distribution Type	1 x 4 splitter
Enclosure Color	Black
Forward Port Type	Hardened mini-size (DLX) adapter
Forward Port, quantity	4
Mounting	Handhole   Pedestal   Pole
Port Type	Hardened multi-fiber (HMFOC) jack, male/pinned
Port, quantity	4
Reverse Port Type	Hardened mini-size DLX
Reverse Port, quantity	1
Splitter, quantity	1
Stub Type	Hardened multi-fiber (HMFOC) plug


### Dimensions

Height	297.8 mm   11.724 in
Width	130.3 mm   5.13 in

# NDX-06BTMOU-A1500F

Depth	90.4 mm   3.559 in
Cable Length, stub	1500 ft (457 m)
Cable Outer Diameter	4.5 x 8.1 mm (0.18 x 0.32 in)

## Dimension Drawing



## Ordering Tree

# NDX-06BTMOU-A1500F

NDX-

-

F

Terminal Model

O6

1 x 4 splitter with reverse

10

1 x 8 splitter with reverse

D1

Index only, 1F with reverse

B2

Branching, 2F

B3

Branching, 3F

B4

Branching, 4F

B5

Branching, 5F

B6

Branching, 6F

M2

Multi-use, 2F with reverse

M3

Multi-use, 3F with reverse

M4

Multi-use, 4F with reverse

Housing Type

B

Mini indexing terminal

H

4x3 MST indexing terminal

Connector Type Housing

T

DLX adapters and 1 HMFOC

G

Full-size Adapters and 1 HMFOC

D

Index only, 1 HMFOC, 1 DLX, 1 DLX (reverse)

E

Index only, 1 HMFOC, 1 Full-size, 1 Full-size (reverse)

H

Branching, 2 HMFOC (only available for housing type "B")

Cable Length

0010

10 feet

0500

500 feet

0050

50 feet

0600

600 feet

0100

100 feet

0750

750 feet

0150

150 feet

1000

1000 feet

0200

200 feet

1250

1250 feet

0250

250 feet

1500

1500 feet

0350

350 feet

1750

1750 feet

0450

450 feet

2000

2000 feet

Cable Type

A

Buried dielectric

Mounting Style

U

Universal (cable stub spool off reel first)

\*0-99 FT length of cable is automatically coiled and packaged 2 units per box. Lengths greater than 99 FT are spooled.

Tail End

MO

HMFOC stub end

M1

2x12 HMFOC stub end

## Material Specifications

Enclosure Material Type

Gasketed hardened plastic

## Optical Specifications

Fiber Type	G.652.D
Operating Wavelength Range	1260 – 1635 nm
Attenuation Cable Coefficient, maximum	0.30 dB/km @ 1550 nm   0.40 dB/km @ 1310 nm
Attenuation Splitter, maximum	7.1 dB
Attenuation Terminal Connectors, maximum	0.45 dB
Directivity, minimum	60 dB
Uniformity, maximum	0.8 dB
Insertion Loss, Splitter, typical	6.7 dB
Insertion Loss, Stub Connector, maximum	0.45 dB
Insertion Loss, Stub Connector, typical	0.16 dB
Insertion Loss, Terminal Connector, typical	0.16 dB
Return Loss, Connector, minimum	65 dB

# NDX-06BTMOU-A1500F

Return Loss, Single Ports, minimum	55 dB
------------------------------------	-------

## Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	5%–100%, condensing
Environmental Space	Above ground   Below ground   Buried
Flammability Rating	UL 94 V-0
Qualification Standards	IEC 60529, IP68 + 2 m waterhead   NEMA, Type 6 + 10 ft waterhead   Telcordia GR-3120-CORE   Telcordia GR-326-CORE   Telcordia GR-771-CORE
UV Resistance	UV stabilized

## Packaging and Weights

Included	Enclosure (1)   Optical splitter (1)   Universal mounting bracket (1)
Packaging quantity	1
Packaging Type	Box   Carton
Weight, without cable	1 kg   2.205 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## Included Products

MST-UMB-MINI	–	DLX® Mini-MST, Fiber Optic Universal Mounting Bracket
--------------	---	-------------------------------------------------------